
PX3111

Pressure transmitter with ceramic measuring cell









Product characteristics		
Number of inputs and outputs		Number of analog outputs: 1
Measuring range	[psi]	03000
Process connection		threaded connection 1/4" NPT external thread Internal thread:M5
Application		
System		gold-plated contacts
Application		for industrial applications
Media		liquids and gases
Conditionally suitable for		use in gases at pressures > 25 bar only on request
Medium temperature	[°C]	-2590
Min. bursting pressure	[psi]	12300
Pressure rating	[psi]	5800
Type of pressure		relative pressure
Electrical data		
Operating voltage	[V]	9.632 DC
Min. insulation resistance	$[M\Omega]$	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Inputs / outputs		
Number of inputs and outputs		Number of analog outputs: 1
Outputs		
Total number of outputs		1
Output signal		analog signal
Number of analog outputs		1

PX3111

Pressure transmitter with ceramic measuring cell



PA-300PSBN14-A-ZVG/US/ /V

Analog current output [mA]	420		
Max. load [Ω]	720; (Ub = 24 V; (Ub - 9,6 V) / 20 mA)		
Overload protection		yes	
Measuring/setting range			
Measuring range [psi]		03000	
Accuracy / deviations			
Repeatability [% of the span]	< 0,15; (with t	temperature fluctuations < 10 K)	
Characteristics deviation [% of the span]	$<\pm$ 0,35 (BFSL) / $<\pm$ 0,75 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)		
Long-term stability [% of the span]	< ± 0,05; (per 6 months)		
Temperature coefficient zero point	0,2; (080 °C)		
[% of the span / 10 K]	-,-, (
Temperature coefficient span [% of the span / 10 K]	0,3; (080 °C)		
Reaction times			
Step response time analog [ms] output	3		
Operating conditions			
Ambient temperature [°C]		-2580	
Storage temperature [°C]		-40100	
Protection	IP 68; IP 69K		
Tests / approvals			
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD	
	EN 61000-4-3 HF radiated	30 V/m	
	EN 61000-4-4 Burst	2 kV	
	EN 61000-4-6 HF conducted	10 V	
	radiation of interference	according to the automotive directive 2004/104/EC / CISPR 25	
	noise immunity	according to the automotive directive 2004/104/EC / ISO 11452-2	
	HF radiated	100 V/m	
	pulse resistance	ISO 7637-2 / severity level 3	
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)	
Vibration resistance	DIN IEC 68-2-6	20 g (102000 Hz)	
MTTF [years]		555	
Pressure equipment directive	sound engineering practice; can be	be used for group 2 fluids; group 1 fluids on request	
Mechanical data			
Weight [g]		213	
Material	stainless steel (1.4404 / 316L); FKM; PA; EPDM/X		
Materials (wetted parts)	stainless steel (1.4305 / 303); ceramics; FKM		
Min. pressure cycles	100 million		
Process connection	threaded connection 1/4	threaded connection 1/4" NPT external thread Internal thread:M5	
Restrictor element integrated	no (can be retrofitted)		

PX3111

Pressure transmitter with ceramic measuring cell



PA-300PSBN14-A-ZVG/US/ /V

Remarks	
Pack quantity	1 pcs.
Electrical connection	
Connector: 1 x M12; coding: A; Conta	acts: gold-plated
2 1	
3 4	



