
PX9227

Pressure transmitter with ceramic measuring cell



PA-001PRBN14-C-DVG/US/ /V



$\mathsf{C} \in \operatorname{COL}_{\mathrm{LISTED}}^{\mathrm{C}} \operatorname{US}_{\mathrm{LA}}^{\mathrm{US}}$

Product characteristics				
Number of inputs and outputs		Number of analog outputs: 1		
Measuring range	[psi]	015		
Process connection		threaded connection 1/4" NPT Internal thread		
Application				
System		gold-plated contacts		
Application		for industrial applications		
Media		liquids and gases		
Medium temperature	[°C]	-2590		
Min. bursting pressure	[psi]	450		
Pressure rating	[psi]	145		
Type of pressure		relative pressure		
Electrical data				
Operating voltage	[V]	1030 DC		
Current consumption	[mA]	< 18		
Min. insulation resistance	[MΩ]	100; (500 V DC)		
Protection class		III		
Reverse polarity protection		yes		
Inputs / outputs				
Number of inputs and outputs		Number of analog outputs: 1		
Outputs				
Total number of outputs		1		
Output signal		analog signal		
Number of analog outputs		1		

PX9227

Pressure transmitter with ceramic measuring cell



PA-001PRBN14-C-DVG/US/ /V

Analog voltage output [V]	15		
Min. load resistance [Ω]	2000		
Overload protection	yes		
Measuring/setting range			
Measuring range [psi]		015	
Accuracy / deviations			
Repeatability [% of the span]	< 0,1; (with temperature fluctuations < 10 K)		
Characteristics deviation [% of the span]	$< \pm 0.25$ (BFSL) / $< \pm 0.5$ (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)		
Long-term stability [% of the span]	< ± 0,05; (per 6 months)		
Temperature coefficient zero point	0,1; (080 °C)		
[% of the span / 10 K]			
Temperature coefficient span [% of the span / 10 K]	0,2; (080 °C)		
Reaction times			
Step response time analog [ms] output	3		
Operating conditions			
Ambient temperature [°C]		-2580	
Storage temperature [°C]	-40100		
Protection	IP 65		
Tests / approvals			
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD	
	EN 61000-4-3 HF radiated	30 V/m	
	EN 61000-4-4 Burst	2 kV	
	EN 61000-4-6 HF conducted	10 V	
	radiation of interference	according to the automotive directive 2004/104/EC / CISPR 25	
	noise immunity	according to the automotive directive 2004/104/EC / ISO 11452-2	
	HF radiated	100 V/m	
	pulse resistance	ISO 7637-2 / severity level 3	
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)	
Vibration resistance	DIN IEC 68-2-6	20 g (102000 Hz)	
MTTF [years]		550	
Pressure equipment directive sound engineering practice; can be used for group 2 fluids; group 1 fluids on re			
Mechanical data			
Weight [g]	222		
Material	stainless steel (1.4404 / 316L); FKM; PA; EPDM/X		
Materials (wetted parts)	stainless steel (1.4305 / 303); ceramics; FKM		
Min. pressure cycles	100 million		
Process connection	threaded connection 1/4" NPT Internal thread		
Restrictor element integrated	no (can be retrofitted)		

PX9227

Pressure transmitter with ceramic measuring cell



