


R2D200



Radar area sensor

R2DBAF6KG/US/IO-Link



Product characteristics	
Communication interface	IO-Link
Housing	rectangular
Dimensions [mm]	80 x 80 x 45
Digital	
Electrical design	PNP/NPN; (configurable)
Output function	normally open / closed; (configurable)
Application	
Radio approval for	EU/RED; Great Britain; Australia; Mexico; Namibia; New Zealand; South Africa; Hong Kong; USA; Canada; Chile; Brazil; Ecuador; Cameroon
Note on radio approval	The list of countries applying the European Radio Equipment Directive 2014/53/EU (RED) can be found under "Downloads".
Electrical data	
Operating voltage [V]	10...30 DC; (to SELV/PELV ; energy-limited circuits according to IEC/UL 61010-1 3rd ed. cl. 9.4)
Current consumption [mA]	< 300; (mean value: 150 mA)

R2D200



Radar area sensor

R2DBAF6KG/US/IO-Link

Power consumption [W]	21; (maximum)
Protection class	III
Reverse polarity protection	yes
Max. power-on delay time [ms]	1000
Operating frequency [GHz]	77...81
Maximum radiated average power spectral density EIRP [dBm/MHz]	-9
Radiated peak power EIRP [dBm]	27

Inputs / outputs

Total number of inputs and outputs	3
------------------------------------	---

Inputs

Inputs	IN1	activation/deactivation of the radar
--------	-----	--------------------------------------

Outputs

Total number of outputs	2	
Output signal	OUT1	switching signal; IO-Link
	OUT2	switching signal; analog signal
Short-circuit protection	yes	
Type of short-circuit protection	yes (non-latching)	
Overload protection	yes	

Analog

Analog current output [mA]	4...20, invertible; (scalable)
Max. load [Ω]	500; (< 250 Ω : Ub 16...30 V DC; 250...500 Ω : Ub 18...30 V DC)
Analog voltage output [V]	0...10, invertible; (scalable)
Min. load [Ω]	2000

Digital

Electrical design	PNP/NPN; (configurable)
Output function	normally open / closed; (configurable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200

Monitoring range

Range [m]	0.1...50; (based on E23014)
Angle of aperture cylindrical [°]	Horizontal 140
	vertical 30

Measuring/setting range

Measuring range [m]	0.1...50; (see diagram:)
Sampling rate [Hz]	20

Accuracy / deviations

Hysteresis [mm]	5; (configurable)
Temperature coefficient analog output [% of the span / 10 K]	$\pm 0,1$

R2D200



Radar area sensor

R2DBAF6KG/US/IO-Link

Repeatability analog output [% of the span]	< 0,1
Linearity error of analog output [% of the span]	± 0,15
Precision analog output [% of the span]	± 0,2 (in addition to the accuracy specifications in the further data section)

Software / programming

Parameter setting options	only via IO-Link
---------------------------	------------------

Interfaces

Communication interface	IO-Link	
Transmission type	COM3 (230,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
Profiles	BLOB	Binary Large Object transfer
	Common - I&D	Identification and Diagnosis
	Function	Locator
	Function	ProductURI
SIO mode	yes	
Required master port class	A	
Min. process cycle time [ms]	3.2	
IO-Link process data (cyclical)	Function	bit length
	Distance	32
	speed	32
	Power	8
	RCS	8
	sensor inclination	1
	device status	4
	binary switching information	4
	IO-Link functions (acyclical)	application specific tag; operating hours counter; number of trigger events; internal temperature; ROI setting; switch-on delays; transmitter can be switched off
Supported DeviceIDs	Type of operation	DeviceID
	default	1519
Note	For further information please see the IODD PDF file at "Downloads"	

Operating conditions

Ambient temperature [°C]	-40...80
Note on ambient temperature	without using the analog output: -40...85 °C
Storage temperature [°C]	-40...85
Protection	IP 65; IP 66; IP 67; IP 69K; (with mounted connectors or protective caps)

Tests / approvals

EMC	DIN EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	DIN EN 61000-4-3 HF radiated	10 V/m
	DIN EN 61000-4-4 Burst	2 kV
	DIN EN 61000-4-6 HF conducted	10 V
	DIN EN 61000-6-2	noise immunity / industrial environments
	EN 55032 emission	class A
Impact resistance	IEC 62262	IK06 (1J)
Vibration resistance	DIN EN 60068-2-6 Fc	10 g 10 frequency cycles, 1 octave/minute, in 3 axes

R2D200



Radar area sensor

R2DBAF6KG/US/IO-Link

Shock resistance	DIN EN 60068-2-27 Ea	50 g 11 ms half-sine; 10 shocks each in every direction along the 3 coordinate axes
Continuous shock resistance	DIN EN 60068-2-29 Eb	40 g 6 ms half-sine; 4,000 shocks each in every direction along the 3 coordinate axes
Fast temperature changes	DIN EN 60068-2-14 Na	TA = -40°C; TB = 85°C; t1 = 30 min; t2 = < 30 s; 300 cycles
Salt spray test	DIN EN 60068-2-11 Ka	8 test cycles
Electrical safety	DIN EN 61010-2-201	electric shock / electrical supply only via SELV/PELV circuits
MTTF [years]		53
UL approval	Ta	-40...65 °C
	File number UL	E205959

Mechanical data

Weight [g]	397.2
Housing	rectangular
Mounting	flush mountable
Dimensions [mm]	80 x 80 x 45
Material	housing: PA; radome: PEI; sealing: HNBR

Displays / operating elements


Display	Switching status	2x LED, yellow
	Power	1x LED, green
	errors	1x LED, red

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connection



Connector: 1 x M12; coding: A; Contacts: 5



1	L+
2	OUT2 Switching output analog output
4	OUT1 Switching output IO-Link
5	IN1 activation/deactivation of the radar
3	L-

R2D200




Radar area sensor

R2DBAF6KG/US/IO-Link

Other data		
Operating mode	standard	Long range, high velocity
max. distance	0.1...20 m	0.25...35 m
distance resolution	100 mm	350 mm
horizontal angular resolution (azimuth)	10 °	10 °
distance accuracy	± 5 mm	± 15 mm
max. velocity	± 6 m/s	± 15 m/s
velocity resolution	± 0.20 m/s	± 0.38 m/s
speed accuracy	± 0.01 m/s	± 0.04 m/s
Sampling rate	20 Hz	20 Hz
Distance	based on E23013	
Resolution	for the detection of two objects of the same size	
Accuracy	for a strong, point-shaped target	

Diagrams and graphs

Monitoring range



1: azimuth

2: elevation

conditions

Reflector: 4.3" Trihedral Corner Reflector (SAJ043-S1)

RCS: 10 dBm²

Distance: 5 m

operating frequency: 79 GHz