
RA6004

Incremental encoder with hollow shaft

RA-0030-I24/N6

Article no longer available - archive entry

Alternative articles: RA3101 + EVC546
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Resolution		30 resolution
Shaft design		hollow shaft open to one side
Shaft diameter	[mm]	6
Application		
Function principle		incremental
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	150
Outputs		
Electrical design		HTL
Max. current load per output	[mA]	50
Switching frequency	[kHz]	160
Type of short-circuit protection		< 60 s
Phase difference A und B	[°]	90
Measuring/setting range		
Resolution		30 resolution
Operating conditions		
Ambient temperature	[°C]	-30...70
Max. relative air humidity	[%]	75; (briefly: 95 %)
Protection		IP 64
Tests / approvals		
Shock resistance		100 g (6 ms)
Vibration resistance		10 g (55...2000 Hz)

RA6004

Incremental encoder with hollow shaft

RA-0030-I24/N6

Mechanical data		
Weight	[g]	490
Dimensions	[mm]	Ø 35 / L = 42.1
Material		aluminum
Max. revolution, mechanical	[U/min]	10000
Max. starting torque	[Nm]	2.5
Reference temperature torque	[°C]	20
Shaft design		hollow shaft open to one side
Shaft diameter	[mm]	6
Shaft fit		H7
Shaft material		steel (1.4104)
Installation depth/shaft	[mm]	6...21
Max. axial shaft misalignment	[mm]	0,5


Electrical connection

Cable: 6 m, PUR; radial, can also be used axially

brown	A
green	0 V A
grey	B
pink	0 V B
red	0 index
black	0 V 0 index
brown/green	L+ (Up)
white/green	L- 0V (Un)
lilac	error inverted
screen	housing

Diagrams and graphs

Pulse diagram



Direction of rotation clockwise (looking at the shaft)