

# PN2599



## Pressure sensor with display

PN-1-1BREG14-MFRKG/US/ IV



- 1 alphanumeric display 4-digit red/green
- 2 LEDs Display unit / Switching status
- 3 Programming button
- 4 upper part of the housing can be rotated 345°
- 5 sealing



### Product characteristics

|                              |   |                   |                  |                   |                  |                |
|------------------------------|---|-------------------|------------------|-------------------|------------------|----------------|
| Number of inputs and outputs | Number of digital outputs: 2; Number of analog outputs: 1                         |                   |                  |                   |                  |                |
| Measuring range              | -1...1 bar  | -1000...1000 mbar | -14.5...14.5 psi | -29.5...29.5 inHg | -401...401 inH2O | -100...100 kPa |
| Process connection           | threaded connection G 1/4 external thread (DIN EN ISO 1179-2); Internal thread:M5 |                   |                  |                   |                  |                |

### Application

|                         |  |         |  |          |  |  |
|-------------------------|--|---------|--|----------|--|--|
| Special feature         | gold-plated contacts                       |         |  |          |  |  |
| Measuring element       | ceramic-capacitive pressure measuring cell |         |  |          |  |  |
| Application             | for industrial applications                |         |  |          |  |  |
| Media                   | liquids and gases                          |         |  |          |  |  |
| Medium temperature [°C] | -25...80                                   |         |  |          |  |  |
| Min. burst pressure     | 30000 mbar                                 | 450 psi |  | 3000 kPa |  |  |
| Pressure rating         | 10000 mbar                                 | 145 psi |  | 1000 kPa |  |  |
| Vacuum resistance       | -1000 mbar                                 |         |  | -0.1 MPa |  |  |
| Type of pressure        | relative pressure; vacuum                  |         |  |          |  |  |

### Electrical data

|                                 |                            |  |  |  |  |  |
|---------------------------------|----------------------------|--|--|--|--|--|
| Operating voltage [V]           | 18...30 DC; (to SELV/PELV) |  |  |  |  |  |
| Current consumption [mA]        | < 35                       |  |  |  |  |  |
| Min. insulation resistance [MΩ] | 100; (500 V DC)            |  |  |  |  |  |
| Protection class                | III                        |  |  |  |  |  |

# PN2599



## Pressure sensor with display

PN-1-1BREG14-MFRKG/US/ IV

|                             |     |
|-----------------------------|-----|
| Reverse polarity protection | yes |
| Power-on delay time [s]     | 0.3 |
| Integrated watchdog         | yes |

### Inputs / outputs

|                              |   |
|------------------------------|---|
| Number of inputs and outputs | Number of digital outputs: 2; Number of analog outputs: 1 |
|------------------------------|---|

### Outputs

|  |  |
|--|--|
| Total number of outputs                              | 2  |
| Output signal  | switching signal; analog signal; IO-Link; (configurable) |
| Electrical design                                    | PNP/NPN  |
| Number of digital outputs                            | 2  |
| Output function                                      | normally open / closed; (configurable)                   |
| Max. voltage drop switching output DC [V]            | 2  |
| Permanent current rating of switching output DC [mA] | 250  |
| Switching frequency DC [Hz]                          | < 500  |
| Number of analog outputs                             | 1  |
| Analog current output [mA]                           | 4...20; (scalable 1:5)                                   |
| Max. load [Ω]  | 500  |
| Analog voltage output [V]                            | 0...10; (scalable 1:5)                                   |
| Min. load resistance [Ω]                             | 2000   |
| Short-circuit protection                             | yes  |
| Type of short-circuit protection                     | yes (non-latching)                                       |
| Overload protection                                  | yes  |

### Measuring/setting range

|                    |                  |                   |                   |                   |                  |                |
|--------------------|------------------|-------------------|-------------------|-------------------|------------------|----------------|
| Measuring range    | -1...1 bar       | -1000...1000 mbar | -14.5...14.5 psi  | -29.5...29.5 inHg | -401...401 inH2O | -100...100 kPa |
| Analog start point | -1000...600 mbar | -14.5...8.7 psi   | -29.5...17.7 inHg | -402...240 inH2O  | -100...60 kPa    |                |
| Analog end point   | -600...1000 mbar | -8.7...14.5 psi   | -17.7...29.5 inHg | -240...402 inH2O  | -60...100 kPa    |                |

### Factory setting / CMPT = 2

|                                   |                  |                   |                   |                  |                 |
|-----------------------------------|------------------|-------------------|-------------------|------------------|-----------------|
| Set point SP                      | -985...1000 mbar | -14.3...14.5 psi  | -29.2...29.5 inHg | -396...402 inH2O | -98.5...100 kPa |
| Reset point rP                    | -995...990 mbar  | -14.45...14.4 psi | -29.4...29.3 inHg | -400...398 inH2O | -99.5...99 kPa  |
| Min. difference between SP and rP | 10 mbar          | 0.15 psi          | 0.3 inHg          | 4 inH2O          | 1 kPa           |
| In steps of                       | 5 mbar           | 0.05 psi          | 0.1 inHg          | 2 inH2O          | 0.5 kPa         |

### Status\_B High Resolution / CMPT = 3

|                                   |                  |                    |                   |                  |                  |
|-----------------------------------|------------------|--------------------|-------------------|------------------|------------------|
| Set point SP                      | -987...1000 mbar | -14.32...14.5 psi  | -29.2...29.5 inHg | -396...401 inH2O | -98.7...100 kPa  |
| Reset point rP                    | -996...992 mbar  | -14.44...14.38 psi | -29.4...29.3 inHg | -400...398 inH2O | -99.6...99.2 kPa |
| Min. difference between SP and rP | 9 mbar           | 0.12 psi           | 0.3 inHg          | 4 inH2O          | 0.9 kPa          |
| In steps of                       | 1 mbar           | 0.01 psi           | 0.1 inHg          | 1 inH2O          | 0.1 kPa          |

### Accuracy / deviations

|                                       |  |
|---------------------------------------|--|
| Switch point accuracy [% of the span] | < ± 0,4; (Turn down 1:1)                                       |
| Repeatability [% of the span]         | < ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1) |

# PN2599



## Pressure sensor with display

PN-1-1BREG14-MFRKG/US/ IV

|  |  |
|--|--|
| Characteristics deviation<br>[% of the span]                 | $< \pm 0,25$ (BFSL) / $< \pm 0,5$ (LS); (Turn down 1:1; BFSL = Best Fit Straight Line; LS = limit value setting) |
| Hysteresis deviation<br>[% of the span]                      | $< \pm 0,1$ ; (Turn down 1:1)  |
| Long-term stability<br>[% of the span]                       | $< \pm 0,05$ ; (Turn down 1:1; per 6 months)   |
| Temperature coefficient zero point<br>[% of the span / 10 K] | $< \pm 0,2$ ; (-0...80 °C)   |
| Temperature coefficient span<br>[% of the span / 10 K]       | $< \pm 0,2$ ; (-0...80 °C)   |
| Notes on the accuracy / deviation                            | switch point accuracy, linearity error under DNV GL: $< \pm 1\%$ ; $< \pm 1\%$                                   |

### Reaction times

|                                       |         |
|---------------------------------------|---------|
| Response time [ms]                    | $< 1.5$ |
| Delay time programmable dS, dr [s]    | 0...50  |
| Damping process value dAP [s]         | 0...4   |
| Damping for the analog output dAA [s] | 0...4   |
| Max. response time analog output [ms] | 3       |

### Software / programming

|                           |   |
|---------------------------|---|
| Parameter setting options | hysteresis / window; normally open / closed; switch-on/ switch-off delay; Damping; Display unit; current/voltage output |
|---------------------------|---|

### Interfaces

| Communication interface             | IO-Link  |                   |          |                            |     |                                     |     |
|-------------------------------------|--|-------------------|----------|----------------------------|-----|-------------------------------------|-----|
| Transmission type                   | COM2 (38,4 kBaud)  |                   |          |                            |     |                                     |     |
| IO-Link revision                    | 1.1  |                   |          |                            |     |                                     |     |
| SDCI standard                       | IEC 61131-9  |                   |          |                            |     |                                     |     |
| SIO mode                            | yes  |                   |          |                            |     |                                     |     |
| Required master port class          | A; (when pin 2 not connected: B)   |                   |          |                            |     |                                     |     |
| Supported DeviceIDs                 | <table border="1"> <thead> <tr> <th>Type of operation</th> <th>DeviceID</th> </tr> </thead> <tbody> <tr> <td>Factory setting / CMPT = 2</td> <td>467</td> </tr> <tr> <td>Status_B High Resolution / CMPT = 3</td> <td>983</td> </tr> </tbody> </table> | Type of operation | DeviceID | Factory setting / CMPT = 2 | 467 | Status_B High Resolution / CMPT = 3 | 983 |
| Type of operation                   | DeviceID   |                   |          |                            |     |                                     |     |
| Factory setting / CMPT = 2          | 467  |                   |          |                            |     |                                     |     |
| Status_B High Resolution / CMPT = 3 | 983  |                   |          |                            |     |                                     |     |
| Note                                | For further information please see the IODD PDF file at "Downloads"  |                   |          |                            |     |                                     |     |

### Factory setting / CMPT = 2

|                                    |                              |                         |
|------------------------------------|------------------------------|-------------------------|
| Profiles                           | Smart Sensor - SSP 0         | Generic Profiled Sensor |
|                                    | Function                     | Device identification   |
|                                    | Function                     | Process data variable   |
|                                    | Function                     | Device diagnosis        |
| Min. process cycle time [ms]       | 2.3                          |                         |
| IO-Link resolution pressure [mbar] | 1                            |                         |
| IO-Link process data (cyclical)    | <b>Function</b>              | <b>bit length</b>       |
|                                    | pressure                     | 14                      |
|                                    | binary switching information | 2                       |
| IO-Link functions (acyclical)      | application specific tag     |                         |

# PN2599



## Pressure sensor with display

PN-1-1BREG14-MFRKG/US/ IV

| Status_B High Resolution / CMPT = 3                     |  |  |
|---|--|--|
| Profiles  | Smart Sensor - SSP 3.1<br>Common - I&D   | Measuring Sensor<br>Identification and Diagnosis |
| Min. process cycle time [ms]                            |  | 3  |
| IO-Link resolution pressure [mbar]                      |  | 1  |
| IO-Link process data (cyclical)                         | <b>Function</b>  | <b>bit length</b>                                |
|   | pressure   | 16   |
|   | device status  | 4  |
|   | binary switching information   | 2  |
| IO-Link functions (acyclical)                           | application specific tag   |  |
| Operating conditions                                    |  |  |
| Ambient temperature [°C]                                |  | -25...80   |
| Storage temperature [°C]                                |  | -40...100  |
| Protection  |  | IP 65; IP 67                                     |
| Tests / approvals                                       |  |  |
| EMC   | DIN EN 61000-6-2<br>DIN EN 61000-6-3   |  |
| Shock resistance  | DIN EN 60068-2-27  | 50 g (11 ms)                                     |
| Vibration resistance                                    | DIN EN 60068-2-6   | 20 g (10...2000 Hz)                              |
| MTTF [years]  |  | 138  |
| UL approval   | UL approval number   | J012   |
| Pressure equipment directive                            | sound engineering practice; can be used for group 2 fluids; group 1 fluids on request      |  |
| Mechanical data   |  |  |
| Weight [g]  |  | 264.5  |
| Housing   |  | tubular  |
| Dimensions [mm]   |  | Ø 34 / L = 92.7                                  |
| Material  | stainless steel (1.4404 / 316L); PBT+PC-GF30; PBT-GF20; PC                                 |  |
| Materials (wetted parts)                                | stainless steel (1.4404 / 316L); Al2O3 (ceramics); FKM                                     |  |
| Min. pressure cycles                                    |  | 100 million                                      |
| Tightening torque [Nm]                                  | 25...35; (recommended tightening torque; Depends on lubrication, seal and pressure rating) |  |
| Process connection                                      | threaded connection G 1/4 external thread (DIN EN ISO 1179-2); Internal thread:M5          |  |
| Process connection sealing                              | FKM (DIN EN ISO 1179-2)  |  |
| Restrictor element integrated                           | no (can be retrofitted)  |  |
| Displays / operating elements                           |  |  |
| Display   | Display unit   | 5 x LED, green (mbar, psi, kPa, inH2O, inHg)     |
|   | Switching status   | 2 x LED, yellow                                  |
|   | Measured values  | alphanumeric display, red/green 4-digit          |
| Remarks   |  |  |
| Pack quantity   |  | 1 pcs.   |
| Electrical connection                                   |  |  |
| Connector: 1 x M12; coding: A; Contacts: 4, gold-plated |  |  |
|   |  |  |

# PN2599



## Pressure sensor with display

PN-1-1BREG14-MFRKG/US/ IV

### Connection



|      |                  |
|------|------------------|
| OUT1 | Switching output |
|      | IO-Link          |
| OUT2 | Switching output |
|      | analog output    |
|      | Core colors :    |
| BK = | black            |
| BN = | brown            |
| BU = | blue             |
| WH = | white            |