

RM6101




Absolute multiturn encoder with solid shaft

RM-8192-S24/N1A

Article to be discontinued

Alternative articles: RM8001

When selecting an alternative article and accessories please note that technical data may differ!



M4 Depth 5 mm



Product characteristics

Resolution	8192 resolution; 8192 steps; 4096 revolutions; 25 bit
Communication interface	SSI data interface
Shaft design	solid shaft
Shaft diameter [mm]	6

Application

Function principle	absolute
Revolution type	multiturn

Electrical data

Operating voltage [V]	4.75...30 DC
Current consumption [mA]	< 200

Outputs

Code	Gray code; (increasing code values when turned clockwise (seen on the shaft))
Code signal	Clock input; TTL-compatible signals; clock and clock (inv.) from drivers to RS 485; data output; synchronous serial; TTL-compatible signal data and data (inv.); incremental signals; 2 sinusoidal incremental signals (A and B) ; phase shifted by 90°; 1 Vss 512 signal periods per revolution

Measuring/setting range

Resolution	8192 resolution; 8192 steps; 4096 revolutions; 25 bit
------------	---

Interfaces

Communication interface	SSI data interface
-------------------------	--------------------

RM6101



Absolute multiturn encoder with solid shaft

RM-8192-S24/N1A

Operating conditions		
Ambient temperature	[°C]	-40...85
Max. relative air humidity	[%]	75; (briefly: 95 %)
Protection		IP 64
Tests / approvals		
Shock resistance		100 g (6 ms)
Vibration resistance		30 g (55...2000 Hz)
MTTF	[years]	46
Mechanical data		
Weight	[g]	459.2
Dimensions	[mm]	Ø 58 / L = 46.7
Material		aluminum
Max. revolution, mechanical	[U/min]	12000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	6
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20
Remarks		
Remarks		Wires/pins not connected (n.c.) must not be used.
Electrical connection		
Cable: 1 m, PUR; Maximum cable length: 100 m; radial, can also be used axially		
black	n.c.	
red	n.c.	
green	n.c.	
brown	n.c.	
brown/green	4.75...30 V (Up)	
lilac	clock	
yellow	clock inverted	
screen	housing	
white/green	0V (Un)	
blue / black	B+	
red/black	B-	
grey	data	
green / black	A+	
yellow / black	A-	
pink	data inverted	

RM6101



Absolute multiturn encoder with solid shaft

RM-8192-S24/N1A

Diagrams and graphs

Pulse diagram

