



# RN6020



## Absolute singleturn encoder with solid shaft

RN-2048-G24/L1B

Article no longer available - archive entry



1 M4 Depth 5 mm



### Product characteristics

Resolution	2048 resolution
Communication interface	parallel
Shaft design	solid shaft
Shaft diameter [mm]	10

### Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 250
Max. revolution electrical [U/min]	1500

### Outputs

Electrical design	HTL
Max. current load per output [mA]	20
Type of short-circuit protection	< 60 s
Code	Gray code; (increasing code values when turned clockwise (seen on the shaft))

### Measuring/setting range

Resolution	2048 resolution
------------	-----------------

### Interfaces

Communication interface	parallel
-------------------------	----------

### Operating conditions

Ambient temperature [°C]	-20...70
Storage temperature [°C]	-30...100

# RN6020



## Absolute singleturn encoder with solid shaft

RN-2048-G24/L1B

Max. relative air humidity	[%]	98
Protection		IP 65

### Tests / approvals

Shock resistance		100 g (6 ms)
Vibration resistance		10 g (55...2000 Hz)

### Mechanical data

Dimensions	[mm]	Ø 58 / L = 52
Material		aluminum
Max. revolution, mechanical [U/min]		10000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	10
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20


### Electrical connection

Cable: 1 m, PUR; Maximum cable length: 100 m; axial

brown	10...30V
yellow/brown	10...30V sensor
white	0V
white/yellow	0V sensor
brown/green	bit 12 (MSB)
white/green	bit 11
red/blue	bit 10
grey/pink	bit 9
lilac	bit 8
black	bit 7
red	bit 6
blue	bit 5
pink	bit 4
grey	bit 3
grey/brown	bit 2
white/pink	bit 1
screen	housing

### Diagrams and graphs

Pulse diagram



release A inverted  
release B inverted  
tracks 7...12  
tracks 1...6