



Incremental encoder with solid shaft

RU-1000-I05/P2

Tests / approvals

Shock resistance	100 g (6 ms)
Vibration resistance	10 g (55...2000 Hz)

Mechanical data

Dimensions [mm]	Ø 58 / L = 46
Material	aluminum
Max. revolution, mechanical [U/min]	12000
Max. starting torque [Nm]	1
Reference temperature torque [°C]	20
Shaft design	solid shaft
Shaft diameter [mm]	6
Shaft material	steel (1.4104)
Max. shaft load axial (at the shaft end) [N]	10
Max. shaft load radial (at the shaft end) [N]	20
Fixing flange	Synchro-flange

Electrical connection

Cable: 2 m; axial

Connector: 1 x M23 (ifm 1001.1)



pink (1)	B inverted
blue (2)	L+ sensor
red (3)	0 index
black (4)	0 index inverted
brown (5)	A
green (6)	A inverted
lilac (7)	error inverted
grey (8)	B
Pin 9	n.c.
white/green (10)	0V (Un)
white (11)	0V sensor
brown/green (12)	L+ (Up)
screen	housing

Diagrams and graphs

Pulse diagram

Direction of rotation clockwise (looking at the shaft)