



Incremental encoder with solid shaft

RU-1024-I05/S1

Article no longer available - archive entry



- 1 reference mark
- 2 M4 Depth 5 mm



Product characteristics

Resolution	1024 resolution
Shaft design	solid shaft
Shaft diameter [mm]	6

Electrical data

Operating voltage tolerance [%]	10
Operating voltage [V]	5 DC
Current consumption [mA]	150

Outputs

Electrical design	TTL
Max. current load per output [mA]	20
Switching frequency [kHz]	300
Phase difference A und B [°]	90

Measuring/setting range

Resolution	1024 resolution
------------	-----------------

Operating conditions

Ambient temperature [°C]	-30...100
Note on ambient temperature	firmly laid cable: -30 °C
Storage temperature [°C]	-30...100
Max. relative air humidity [%]	98
Protection	IP 64

RU1079



Incremental encoder with solid shaft

RU-1024-I05/S1

Tests / approvals

Shock resistance	100 g (6 ms)
Vibration resistance	10 g (55...2000 Hz)

Mechanical data

Dimensions [mm]	Ø 58 / L = 46
Material	aluminum
Max. revolution, mechanical [U/min]	12000
Max. starting torque [Nm]	1
Reference temperature torque [°C]	20
Shaft design	solid shaft
Shaft diameter [mm]	6
Shaft material	steel (1.4104)
Max. shaft load axial (at the shaft end) [N]	10
Max. shaft load radial (at the shaft end) [N]	20
Fixing flange	Synchro-flange

Electrical connection

Cable: 1 m, PUR; axial

Connector: 1 x Bajonett (ifm 1000.2)



Pin 1	A
Pin 2	A inverted
Pin 3	B
Pin 4	B inverted
Pin 5	L+ sensor
Pin 6	0 index
Pin 7	0 index inverted
Pin 9	L+ (Up)
Pin 10	0V sensor
Pin 11	housing
Pin 12	0V (Un)

Diagrams and graphs

Pulse diagram	Direction of rotation clockwise (looking at the shaft)
---------------	---