




Pressure switch with ceramic measuring cell

PPA400-SBR14-ASIVG/US/ IV

Article to be discontinued

Alternative articles: PP7550 + AC5225  
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Measuring range	[bar]	0...400
Process connection		threaded connection G 1/4 Internal thread
Application		
System		gold-plated contacts
Design		analog value (16 bit value incl. sign)
Application		for industrial applications
Media		Liquids
Conditionally suitable for		use in gases at pressures > 25 bar only on request
Medium temperature	[°C]	-25...80
Min. bursting pressure	[bar]	1000
Pressure rating	[bar]	600
Type of pressure		relative pressure
Electrical data		
Operating voltage	[V]	18...31.6 DC
Current consumption	[mA]	< 25
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III



## Pressure switch with ceramic measuring cell

PPA400-SBR14-ASIVG/US/ IV

Reverse polarity protection	yes	
Power-on delay time [s]	0.3	
Integrated watchdog	yes	
Outputs		
Electrical design	AS-i	
Overload protection	yes	
Measuring/setting range		
Measuring range [bar]	0...400	
Accuracy / deviations		
Repeatability [% of the span]	< ± 0,1; (with temperature fluctuations < 10 K)	
Characteristics deviation [% of the span]	< ± 1,5; (linearity, incl. hysteresis and repeatability , limit value setting to DIN EN IEC 62828-1)	
Hysteresis deviation [% of the span]	< ± 0,5	
Long-term stability [% of the span]	< ± 0,1; (per year)	
Temperature coefficient zero point [% of the span / 10 K]	0,2; (0...70 °C)	
Temperature coefficient span [% of the span / 10 K]	0,3; (0...70 °C)	
Operating conditions		
Ambient temperature [°C]	-25...70	
Storage temperature [°C]	-40...100	
Protection	IP 67	
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD Klasse B
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	1 kV class A / 2 kV class B
	EN 55011 emission	Level B
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF [years]	293	
Pressure equipment directive	sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data		
Weight [g]	248	
Material	stainless steel (1.4301 / 304); PA	
Materials (wetted parts)	stainless steel (1.4305 / 303); ceramics; FKM	
Min. pressure cycles	100 million	
Process connection	threaded connection G 1/4 Internal thread	
Restrictor element integrated	yes	
Displays / operating elements		
Display	Power	LED, green
	error	LED, red

# PPA020



## Pressure switch with ceramic measuring cell

PPA400-SBR14-ASIVG/US/ IV

### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection

