
## **PS3427**

## Hydrostatic submersible pressure transmitter

SUBMERSIBLE 0,6BAR 15M PUR CABLE





# C€ CA

Number of inputs ar	nd outputs		NI	umber of analog o	nutnuts: 1	
Measuring range		00.6 bar	0600 mbar	08.7 psi	0240.9 inH2O	060 kPa
Application		3	5550 Hibai	00.7 p3i	J240.3 III 120	J00 Ki u
Design			with canilla	ary tube for press	ure compensation	
Application				for industrial appli		
Media				Liquids	ications	
Medium temperatur	e [°C]	-1050				
Min. bursting pressu		4.8 bar	70	psi	480 kPa	
Pressure rating		4 bar		psi	400 kPa	
Type of pressure				relative press	sure	
Electrical data						
Operating voltage	[V]			1030 DC	;	<u> </u>
Protection class		III				
Reverse polarity protection		yes				
Measuring principle		hydrostatic				
Inputs / outputs						
Number of inputs and outputs		Number of analog outputs: 1				
Outputs						
Total number of out	puts			1		
Output signal		analog signal				
Number of analog o	outputs	1				
Analog current outp	ut [mA]	420				
Max. load	[Ω]	700; (Ub = 24 V; (Ub - 10 V) / 20 mA)				
Short-circuit protect	ion			yes		
Measuring/setting	range					
Measuring range		00.6 bar	0600 mbar	08.7 psi	0240.9 inH2O	060 kPa
Accuracy / deviation	ons					
Repeatability	[% of the span]		< 0,1; (wi	th temperature flu	ıctuations < 10 K)	
Characteristics devi	ation [% of the span]	< 0,5 (BFSL) / 1; (incl. linearity, zero and span error (limit value setting))				
Linearity deviation	[% of the span]	< 0,2 (BFSL)				
Long-term stability [% of the span]		< 0,2; (per year)				

## **PS3427**

#### Hydrostatic submersible pressure transmitter



SUBMERSIBLE 0,6BAR 15M PUR CABLE

Temperature coefficient zero point	< ± 0,2; (050 °C)
[% of the span / 10 K]	
Temperature coefficient span [% of the span / 10 K]	< ± 0,2; (050 °C)

Operating conditions		
Ambient temperature	[°C]	-1050
Storage temperature	[°C]	-3080
Protection		IP 68

Tests / approvals			
MTTF	[years]	403	
Pressure equipment directive		sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	


Mechanical data		
Weight	[g]	1246
Material		stainless steel (1.4571/316Ti ); PA

Remarks	
Pack quantity	1 pcs.

#### **Electrical connection**

Cable: 15 m, PUR, Ø 7.5 mm; Core insulation:, PVC

#### Connection



Core colors :

BN = brown

GY = grey

WH = white