
PS3617

Hydrostatic submersible pressure transmitter



SUBMERSIBLE 1BAR 30M PUR CABLE



CE CA

Product characteristics							
Number of inputs and outputs		Number of analog outputs: 1					
Measuring range		01 bar	01000 mbar	014.5 psi	0401.5 inH2O	0100 kPa	
Application							
Design		with capillary tube for pressure compensation					
Application		for industrial applications					
Media		Liquids					
Medium temperature	[°C]	-1050					
Min. bursting pressure		6 bar	87	' psi	600 kPa		
Pressure rating		5 bar	72	2.5 psi	500 kPa		
Type of pressure		relative pressure					
Electrical data							
Operating voltage	[V]	1030 DC					
Protection class			III				
Reverse polarity protection		yes					
Measuring principle		hydrostatic					
Inputs / outputs							
Number of inputs and outputs		Number of analog outputs: 1					
Outputs							
Total number of outputs				1			
Output signal		analog signal					
Number of analog outputs		1					
Analog current output	[mA]			420			
Max. load	[Ω]	700; (Ub = 24 V; (Ub - 10 V) / 20 mA)					
Short-circuit protection		yes					
Measuring/setting range							
Measuring range		01 bar	01000 mbar	014.5 psi	0401.5 inH2O	0100 kPa	
Accuracy / deviations							
Repeatability [% of the	span]	< 0,1; (with temperature fluctuations < 10 K)					
Characteristics deviation [% of the	span]	< 0,5 (BFSL) /1; (incl. linearity, zero and span error (limit value setting))					
Linearity deviation [% of the span]		< 0,2 (BFSL)					
Long-term stability [% of the span]		< 0,2; (per year)					


PS3617

Hydrostatic submersible pressure transmitter

SUBMERSIBLE 1BAR 30M PUR CABLE



Temperature coefficient zero point [% of the span / 10 K]		< ± 0,2; (050 °C)	
Temperature coefficient span [% of the span / 10 K]		< ± 0,2; (050 °C)	
Operating conditions			
Ambient temperature	[°C]	-1050	
Storage temperature	[°C]	-3080	
Protection		IP 68	
Tests / approvals			
MTTF	[years]	403	
Pressure equipment directive		sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data			
Weight	[g]	2342.8	
Material		stainless steel (1.4571/316Ti); PA	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			
Cable: 30 m, PUR, Ø 7.5 r	nm		
Connection			



	Core colors :	
BN =	brown	
BN = GY =	grey	
WH =	white	