


PT5501



Pressure transmitter

PT-250-SEG14-A-ZVG/US



1 sealing



Product characteristics

Number of inputs and outputs	Number of analog outputs: 1		
Measuring range	0...250 bar	0...3625 psi	0...25 MPa
Process connection	threaded connection G 1/4 external thread (DIN EN ISO 1179-2)		

Application

Application	for mobile applications		
Media	liquids and gases		
Medium temperature [°C]	-40...125		
Min. bursting pressure	1200 bar	17400 psi	120 MPa
Pressure rating	625 bar	9060 psi	62.5 MPa
Note on pressure rating	static		
Vacuum resistance [mbar]	-1000		
Type of pressure	relative pressure		

Electrical data

Operating voltage [V]	8...32 DC
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	< 0.1

Inputs / outputs

Number of inputs and outputs	Number of analog outputs: 1
------------------------------	-----------------------------

Outputs

Total number of outputs	1
Output signal	analog signal
Number of analog outputs	1
Analog current output [mA]	4...20
Max. load [Ω]	(U _b - 8 V) / 21,5 mA; @8V = 0 Ω; @12V max. 200 Ω; @24V max. 750 Ω

PT5501



Pressure transmitter

PT-250-SEG14-A-ZVG/US

Short-circuit proof		yes		
Overload protection		yes		
Measuring/setting range				
Measuring range		0...250 bar	0...3625 psi	0...25 MPa
Accuracy / deviations				
Repeatability [% of the span]		< ± 0,05; (with temperature fluctuations < 10 K)		
Characteristics deviation [% of the span]		< ± 0,8; (incl. drift when overtightened, zero point and span error, non-linearity, hysteresis)		
Linearity deviation [% of the span]		< ± 0,25 (BFSL) / < ± 0,5 (LS)		
Hysteresis deviation [% of the span]		< ± 0,2		
Long-term stability [% of the span]		< ± 0,1; (per 6 months)		
Temperature coefficient zero point [% of the span / 10 K]		< ± 0,1 (0...80 °C); < ± 0,2 (-40...0 °C / 80...125 °C)		
Temperature coefficient span [% of the span / 10 K]		< ± 0,1 (0...80 °C); < ± 0,2 (-40...0 °C / 80...125 °C)		
Reaction times				
Step response time analog output [ms]		2		
Operating conditions				
Ambient temperature [°C]		-40...100		
Storage temperature [°C]		-40...100		
Protection		IP 67; IP 69K		
Tests / approvals				
EMC		compliant with UN ECE R10, rev. 5	(E1 compliant)	
		ISO 11452-2	100 V/m	
		DIN EN 61326-1		
Shock resistance		DIN EN 60068-2-27	500 g (1 ms)	
Vibration resistance		DIN EN 60068-2-6	20 g (10...2000 Hz)	
MTTF [years]		704		
UL approval		UL approval number	J072	
		File number UL	E174189	
Pressure equipment directive		sound engineering practice; can be used for group 2 fluids; group 1 fluids on request		
Mechanical data				
Weight [g]		59		
Material		stainless steel (630/1.4542/17-4 PH); stainless steel (1.4404 / 316L); PEI		
Materials (wetted parts)		stainless steel (630/1.4542/17-4 PH)		
Min. pressure cycles		60 million; (at 1.2 times nominal pressure)		
Tightening torque [Nm]		25...35; (recommended tightening torque; Depends on lubrication, seal and pressure rating)		
Process connection		threaded connection G 1/4 external thread (DIN EN ISO 1179-2)		
Process connection sealing		HNBR (DIN EN ISO 1179-2)		
Restrictor element integrated		yes		



Pressure transmitter

PT-250-SEG14-A-ZVG/US

Remarks


Remarks	BFSL = Best Fit Straight Line
	LS = limit value setting
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Maximum cable length: 30 m




Connection



OUT analog output
Colors to DIN EN 60947-5-2
Core colors :
BN = brown
WH = white

Diagrams and graphs

Characteristic load curve current output



1: Max. load
2: Min. load