


PT5315



Pressure transmitter

PT-006-SEG14-A-ZVG/US/ IW



1 sealing



Product characteristics				
Number of inputs and outputs	Number of analog outputs: 1			
Measuring range	0...6 bar	0...87 psi	0...600 kPa	0...0.6 MPa
Process connection	threaded connection G 1/4 external thread (DIN EN ISO 1179-2)			
Application				
Application	for industrial applications			
Media	liquids and gases			
Medium temperature [°C]	-40...90			
Min. bursting pressure	200 bar	2900 psi	20 MPa	
Pressure rating	15 bar	215 psi	1.5 MPa	
Note on pressure rating	static			
Vacuum resistance [mbar]	-1000			
Type of pressure	relative pressure			
Electrical data				
Operating voltage [V]	8.5...36 DC			
Min. insulation resistance [MΩ]	100; (500 V DC)			
Protection class	III			
Reverse polarity protection	yes			
Power-on delay time [s]	< 0.1			
Inputs / outputs				
Number of inputs and outputs	Number of analog outputs: 1			
Outputs				
Total number of outputs	1			
Output signal	analog signal			
Number of analog outputs	1			
Analog current output [mA]	4...20			
Max. load [Ω]	(U _b – 8,5 V) / 21,5 mA; @8,5V= 0 Ω; @12V max. 160 Ω; @24V max. 720 Ω			

PT5315



Pressure transmitter

PT-006-SEG14-A-ZVG/US/ IW

Short-circuit proof	yes
Overload protection	yes
Measuring/setting range	
Measuring range	0...6 bar 0...87 psi 0...600 kPa 0...0.6 MPa
Accuracy / deviations	
Repeatability [% of the span]	$< \pm 0,05$; (with temperature fluctuations < 10 K)
Characteristics deviation [% of the span]	$< \pm 0,5$; (incl. drift when overtightened, zero point and span error, non-linearity, hysteresis)
Linearity deviation [% of the span]	$< \pm 0,1$ (BFSL) / $< \pm 0,2$ (LS)
Hysteresis deviation [% of the span]	$< \pm 0,2$
Long-term stability [% of the span]	$< \pm 0,1$; (per 6 months)
Temperature coefficient zero point and span [% of the span / 10 K]	$< 0,1$ ($-25...90$ °C) / $< 0,2$ ($-40...-25$ °C)
Reaction times	
Step response time analog output [ms]	1
Operating conditions	
Ambient temperature [°C]	$-40...90$
Storage temperature [°C]	$-40...100$
Protection	IP 67; IP 69K
Tests / approvals	
EMC	DIN EN 61000-6-2 DIN EN 61000-6-3
Shock resistance	DIN EN 60068-2-27 50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6 20 g (10...2000 Hz)
MTTF [years]	787
UL approval	UL approval number J029
Pressure equipment directive	sound engineering practice; can be used for group 2 fluids; group 1 fluids on request
Mechanical data	
Weight [g]	58
Material	stainless steel (630/1.4542/17-4 PH); stainless steel (1.4404 / 316L); PEI
Materials (wetted parts)	stainless steel (630/1.4542/17-4 PH)
Min. pressure cycles	60 million; (at 1.2 times nominal pressure)
Tightening torque [Nm]	25...35; (recommended tightening torque; Depends on lubrication, seal and pressure rating)
Process connection	threaded connection G 1/4 external thread (DIN EN ISO 1179-2)
Process connection sealing	FKM (DIN EN ISO 1179-2)
Restrictor element integrated	no (can be retrofitted)
Remarks	
Remarks	BFSL = Best Fit Straight Line LS = limit value setting

PT5315




Pressure transmitter

PT-006-SEG14-A-ZVG/US/ IW


Pack quantity 1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection



OUT analog output
Colors to DIN EN 60947-5-2
Core colors :
BN = brown
BU = blue