



RU6113

Incremental encoder with solid shaft

RU-6000-I24/K R



Article no longer available - archive entry



- 1 reference mark
- 2 M4 Depth 5 mm



Product characteristics

Resolution	6000 resolution
Shaft design	solid shaft
Shaft diameter [mm]	10

Application

Function principle	incremental
--------------------	-------------

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	150

Outputs

Electrical design	HTL
Max. current load per output [mA]	50
Switching frequency [kHz]	300
Type of short-circuit protection	< 60 s
Phase difference A und B [°]	90

Measuring/setting range

Resolution	6000 resolution
------------	-----------------

Operating conditions

Ambient temperature [°C]	-30...85
Storage temperature [°C]	-30...100

RU6113



Incremental encoder with solid shaft

RU-6000-I24/K R

Max. relative air humidity	[%]	98
Protection		IP 64

Tests / approvals


Shock resistance		100 g (6 ms)
Vibration resistance		15 g (55...2000 Hz)

Mechanical data

Weight	[g]	423.2
Dimensions	[mm]	Ø 58 / L = 75.5
Material		aluminum
Max. revolution, mechanical	[U/min]	12000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	10
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20
Fixing flange		Synchro-flange

Electrical connection

Connector: 1 x M23 (ifm 1001.4), radial



1	B inverted
2	L+ sensor
3	0 index
4	0 index inverted
5	A
6	A inverted
screen	housing
7	error inverted
8	B
9	n.c.
10	0V (Un)
11	0V sensor
12	L+

RU6113




Incremental encoder with solid shaft

RU-6000-I24/K R

Diagrams and graphs

Pulse diagram



Direction of rotation clockwise (looking at the shaft)