
# PX3226

### Pressure transmitter with ceramic measuring cell









Product characteristics				
Number of inputs and outputs		Number of analog outputs: 1		
Measuring range	[psi]	030		
Process connection		threaded connection 1/4" NPT external thread Internal thread:M5		
Application				
System		gold-plated contacts		
Application		for industrial applications		
Media		liquids and gases		
Medium temperature	[°C]	-2590		
Min. bursting pressure	[psi]	725		
Pressure rating	[psi]	290		
Type of pressure		relative pressure		
Electrical data				
Operating voltage	[V]	9.632 DC		
Min. insulation resistance	$[M\Omega]$	100; (500 V DC)		
Protection class		III		
Reverse polarity protection		yes		
Inputs / outputs				
Number of inputs and outputs		Number of analog outputs: 1		
Outputs				
Total number of outputs		1		
Output signal		analog signal		
Number of analog outputs		1		

# PX3226

### Pressure transmitter with ceramic measuring cell



PA-003PRBN14-A-ZVG/US/ /V

Analog current output	[mA]	420		
Max. load	[Ω]	720; (Ub = 24 V; (Ub - 9,6 V) / 20 mA)		
Overload protection			yes	
Measuring/setting range				
Measuring range	[psi]		030	
Accuracy / deviations				
Repeatability [% of the span]		< 0,15; (with temperature fluctuations < 10 K)		
Characteristics deviation [% of the span]		$< \pm 0.35$ (BFSL) $/ < \pm 0.75$ (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)		
Long-term stability [% of the span]		< ± 0,05; (per 6 months)		
Temperature coefficient zero point [% of the span / 10 K]		0,2; (080 °C)		
Temperature coefficient span [% of the span / 10 K]		0,3; (080 °C)		
Reaction times				
Step response time analog output	[ms]	3		
Operating conditions				
Ambient temperature	[°C]		-2580	
Storage temperature	[°C]	-40100		
Protection			IP 65	
Tests / approvals				
EMC		EN 61000-4-2 ESD	4 kV CD / 8 kV AD	
		EN 61000-4-3 HF radiated	30 V/m	
		EN 61000-4-4 Burst	2 kV	
		EN 61000-4-6 HF conducted	10 V	
		radiation of interference	according to the automotive directive 2004/104/EC / CISPR 25	
		noise immunity	according to the automotive directive 2004/104/EC / ISO 11452-2	
		HF radiated	100 V/m	
		pulse resistance	ISO 7637-2 / severity level 3	
Shock resistance		DIN IEC 68-2-27	50 g (11 ms)	
Vibration resistance	C	DIN IEC 68-2-6	20 g (102000 Hz)	
	[years]	555		
Pressure equipment directive		sound engineering practice; can be used for group 2 fluids; group 1 fluids on request		
Mechanical data	[m]		010	
Weight	[g]	213		
Material Material (watted a arts)		stainless steel (1.4404 / 316L); FKM; PA; EPDM/X		
Materials (wetted parts)		stainless steel (1.4305 / 303); ceramics; FKM		
Min. pressure cycles		100 million		
Process connection  Restrictor element integrated				
			PT external thread Internal thread:M5 n be retrofitted)	

# PX3226

## Pressure transmitter with ceramic measuring cell



PA-003PRBN14-A-ZVG/US/ /V

Remarks	
Pack quantity	1 pcs.
Electrical connection	
Connector: 1 x M12; coding: A; Conta	acts: gold-plated
3 4	
Connection	

