RV6002


Incremental encoder with solid shaft

RV-0060-I24/L2

Article no longer available - archive entry

Alternative articles: RV3500

When selecting an alternative article and accessories please note that technical data may differ!



1 reference mark
2 M3 Depth 5 mm

Product characteristics		
Resolution		60 resolution
Shaft design		solid shaft
Shaft diameter	[mm]	10
Application		
Function principle		incremental
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	150
Outputs		
Electrical design		HTL
Max. current load per output	[mA]	50
Switching frequency	[kHz]	300
Type of short-circuit protection		< 60 s
Phase difference A und B	[°]	90
Measuring/setting range		
Resolution		60 resolution

RV6002

Incremental encoder with solid shaft

RV-0060-I24/L2

Operating conditions		
Ambient temperature	[°C]	-30...85
Storage temperature	[°C]	-30...100
Max. relative air humidity	[%]	98
Protection		IP 64

Tests / approvals	
Shock resistance	100 g (6 ms)
Vibration resistance	10 g (55...2000 Hz)

Mechanical data		
Weight	[g]	44
Dimensions	[mm]	Ø 58 / L = 46
Material		aluminum
Max. revolution, mechanical	[U/min]	12000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	10
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20


Electrical connection

Cable: 2 m, PUR; axial

brown	A
green	A inverted
grey	B
pink	B inverted
red	0 index
black	0 index inverted
blue	L+ sensor
white	0V sensor
brown/green	L+ (Up)
white/green	0V (Un)
lilac	error inverted
screen	housing

Diagrams and graphs

Pulse diagram



Direction of rotation clockwise (looking at the shaft)