


PX3254



Pressure transmitter with ceramic measuring cell

PA-010PRBN14-A-ZVG/US/ IV

Article no longer available - archive entry



Product characteristics		
Number of inputs and outputs	Number of analog outputs: 1	
Measuring range	[psi]	0...100
Process connection	threaded connection 1/4" NPT external thread Internal thread:M5	
Application		
System	gold-plated contacts	
Application	for industrial applications	
Media	liquids and gases	
Medium temperature	[°C]	-25...90
Min. bursting pressure	[psi]	2175
Pressure rating	[psi]	1087
Type of pressure	relative pressure	
Electrical data		
Operating voltage	[V]	9.6...32 DC
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class	III	
Reverse polarity protection	yes	
Inputs / outputs		
Number of inputs and outputs	Number of analog outputs: 1	
Outputs		
Total number of outputs	1	
Output signal	analog signal	

PX3254



Pressure transmitter with ceramic measuring cell

PA-010PRBN14-A-ZVG/US/ IV

Number of analog outputs	1	
Analog current output [mA]	4...20	
Max. load [Ω]	720; (Ub = 24 V; (Ub - 9,6 V) / 20 mA)	
Overload protection	yes	
Measuring/setting range		
Measuring range [psi]	0...100	
Accuracy / deviations		
Repeatability [% of the span]	< 0,15; (with temperature fluctuations < 10 K)	
Characteristics deviation [% of the span]	< ± 0,35 (BFSL) / < ± 0,75 (LS); (incl. linearity, zero and span error (limit value setting))	
Long-term stability [% of the span]	< ± 0,05; (per 6 months)	
Temperature coefficient zero point [% of the span / 10 K]	0,2; (0...80 °C)	
Temperature coefficient span [% of the span / 10 K]	0,3; (0...80 °C)	
Reaction times		
Step response time analog output [ms]	500	
Operating conditions		
Ambient temperature [°C]	-25...80	
Storage temperature [°C]	-40...100	
Protection	IP 65	
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	30 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	radiation of interference	according to the automotive directive 2004/104/EC / CISPR 25
	noise immunity	according to the automotive directive 2004/104/EC / ISO 11452-2
	HF radiated	100 V/m
	pulse resistance	ISO 7637-2 / severity level 3
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
Mechanical data		
Weight [g]	0.218	
Material	stainless steel (1.4404 / 316L); FKM; PA; EPDM/X	
Materials (wetted parts)	stainless steel (1.4305 / 303); ceramics; FKM	
Min. pressure cycles	100 million	
Process connection	threaded connection 1/4" NPT external thread Internal thread:M5	
Remarks		
Pack quantity	1 pcs.	

PX3254



Pressure transmitter with ceramic measuring cell

PA-010PRBN14-A-ZVG/US/ /V

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

