


PZ9987



Pressure sensor with LED bar display

PZ-001KRBR14-HFPKG/US/...V

Article no longer available - archive entry



- 1 LED display
- 2 Programming button



Product characteristics		
Number of inputs and outputs		Number of digital outputs: 1 0...100 threaded connection G 1/4 Internal thread
Measuring range [kPa]		
Process connection		
Application		
System		gold-plated contacts
Application		for industrial applications
Media		liquids and gases
Medium temperature [°C]		-25...80
Min. bursting pressure [kPa]		3000
Pressure rating [kPa]		1000
Type of pressure		relative pressure
Electrical data		
Operating voltage [V]		18...30 DC
Current consumption [mA]		< 50
Min. insulation resistance [MΩ]		100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Power-on delay time [s]		0.2
Integrated watchdog		yes



Pressure sensor with LED bar display

PZ-001KRBR14-HFPKG/US/...V

Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 1
Outputs		
Total number of outputs		1
Output signal		switching signal
Electrical design		PNP
Number of digital outputs		1
Output function		normally open / closed; (configurable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	10
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Measuring/setting range		
Measuring range	[kPa]	0...100
Set point SP	[kPa]	5...100
Reset point rP	[kPa]	3...98
In steps of	[kPa]	1
Note on hysteresis		adjustable
Accuracy / deviations		
Switch point accuracy		< ± 2,0
	[% of the final value]	
Repeatability		< ± 0,25; (with temperature fluctuations < 10 K)
	[% of the final value]	
Temperature drift per 10 K		< ± 0.3
Software / programming		
Adjustment of the switch point		Programming button
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 65
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
Mechanical data		
Material	EPDM/X; FKM; NBR; PA; PBT; PC; PTFE; stainless steel (1.4301 / 304)	

PZ9987



Pressure sensor with LED bar display

PZ-001KRBR14-HFPKG/US/...V

Materials (wetted parts)	FKM; ceramics; stainless steel (1.4305 / 303)
Min. pressure cycles	100 million
Process connection	threaded connection G 1/4 Internal thread

Displays / operating elements

Display	Switching status	LED, yellow
	Measured values	10 x LED, green Resolution 10 % of the final value

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated

