


RV6120



Incremental encoder with solid shaft

RV-0500-I24/K

Article no longer available - archive entry



Product characteristics	
Resolution	500 resolution
Shaft design	solid shaft
Shaft diameter [mm]	10
Electrical data	
Operating voltage [V]	10...30 DC
Current consumption [mA]	150
Outputs	
Electrical design	HTL
Max. current load per output [mA]	50
Switching frequency [kHz]	160
Type of short-circuit protection	< 60 s
Phase difference A und B [°]	90
Measuring/setting range	
Resolution	500 resolution
Operating conditions	
Ambient temperature [°C]	-30...85
Storage temperature [°C]	-30...100
Max. relative air humidity [%]	98
Protection	IP 64

RV6120




Incremental encoder with solid shaft


RV-0500-I24/K

Tests / approvals		
Shock resistance		100 g (6 ms)
Vibration resistance		15 g (55...2000 Hz)
Mechanical data		
Dimensions	[mm]	Ø 58 / L = 75.5
Material		aluminum
Max. revolution, mechanical	[U/min]	12000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	10
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20
Electrical connection		

Connector: 1 x M23 (ifm 1001.4), radial



1	B inverted
2	L+ sensor
3	0 index
4	0 index inverted
5	A
6	A inverted
7	error inverted
8	B
9	n.c.
10	0V
11	0V sensor
12	L+

Diagrams and graphs	
Pulse diagram	 Direction of rotation clockwise (looking at the shaft)