


**Flow meter with fast response and display**

SBG11KL0FRKG

 **Product characteristics**

Measuring range	1...50 l/min	0.06...3 m³/h	16...793 gph	0.26...13.2 gpm
Process connection	threaded connection G 1 Internal thread			

**Application**

System	gold-plated contacts
Media	Liquids; oils (viscosity 68 mm²/s at 40 °C)
Medium temperature [°C]	-10...100
Pressure rating [bar]	100
Pressure rating [MPa]	10
Note on pressure rating	at medium temperature >70°C: 80 bar / 8 MPa

# SB3244



## Flow meter with fast response and display

SBG11KL0FRKG

Electrical data				
Operating voltage	[V]		18...30 DC; (to SELV/PELV)	
Current consumption	[mA]		< 50	
Protection class			III	
Reverse polarity protection			yes	
Power-on delay time	[s]		< 3	
Outputs				
Total number of outputs			2	
Output signal			switching signal; analog signal; frequency signal; IO-Link	
Output function			normally open / closed; (configurable)	
Max. voltage drop switching output DC	[V]		2	
Max. current load per output	[mA]		150; (200: ...60 °C; Ambient temperature; 250: ...40 °C; Ambient temperature)	
Analog current output	[mA]		4...20	
Max. load	[Ω]		500	
Short-circuit protection			yes	
Overload protection			yes	
Frequency of the output	[Hz]		0...10000	
Measuring/setting range				
Measuring range		1...50 l/min	0.06...3 m³/h	16...793 gph
Display range		0...60 l/min	0...3.6 m³/h	0...15.86 gpm
Resolution		0.01 l/min	0.001 m³/h	0.01 gpm
Set point SP		0.35...50 l/min	0.02...3 m³/h	0.08...13.2 gpm
Reset point rP		0...49.65 l/min	0...2.98 m³/h	0...13.12 gpm
Frequency end point, FEP		3.35...50 l/min	0.2...3 m³/h	0.88...13.2 gpm
In steps of		0.05 l/min	0.005 m³/h	0.02 gpm
Frequency at the end point FRP	[Hz]		10...10000	
In steps of	[Hz]		10	
Measuring dynamics			1:50	
Temperature monitoring				
Measuring range		-10...100 °C		14...212 °F
Display range		-32...122 °C		-25.6...251.6 °F
Resolution		0.1 °C		0.1 °F
Set point SP		-9.3...100 °C		15.2...212 °F
Reset point rP		-10...99.3 °C		14...210.8 °F
In steps of		0.1 °C		0.2 °F
Frequency start point, FSP		-10...78 °C		14...172.4 °F
Frequency end point, FEP		12...100 °C		53.6...212 °F
Frequency at the end point FRP	[Hz]		10...10000	
In steps of	[Hz]		10	
Accuracy / deviations				
Flow monitoring				
Accuracy (in the measuring range)			± 5 % MEW; (Q > 1 l/min; 20...70 °C Medium temperature)	

# SB3244



## Flow meter with fast response and display

SBG11KL0FRKG

Repeatability		± 1 % MEW
Temperature monitoring		
Temperature drift		0,029 °C / K
Accuracy	[K]	3 K (25°C; Q > 1 l/min)
<b>Reaction times</b>		
Flow monitoring		
Response time	[s]	0.01
Damping process value dAP	[s]	0...5
In steps of	[s]	0.1
Damping for the analog output dAA	[s]	0...5
In steps of	[s]	0.1
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 120 (Q > 1 l/min)
<b>Software / programming</b>		
Parameter setting options	hysteresis / window; normally open / closed; switching logic; current/frequency output; damping for the switching output / analog output; display can be rotated and switched off; standard unit of measurement; process value color; calibration factor	
<b>Interfaces</b>		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis	
SIO mode	yes	
Required master port class	A	
Process data analog	2	
Process data binary	2	
Min. process cycle time	[ms]	3.2
Supported DeviceIDs	Type of operation	DeviceID
	default	1045
<b>Operating conditions</b>		
Ambient temperature	[°C]	0...60
Note on ambient temperature	medium temperature < 80 °C medium temperature < 100 °C: 0...40 °C	
Storage temperature	[°C]	-15...80
Protection	IP 65; IP 67	
<b>Tests / approvals</b>		
EMC	DIN EN 61000-6-2 DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[years]	145
UL approval	UL approval number	I006
Pressure equipment directive	sound engineering practice	

# SB3244

## Flow meter with fast response and display

SBG11KL0FRKG



Mechanical data				
Weight	[g]	1583		
Material		stainless steel (1.4404 / 316L); PBT+PC-GF30; PBT-GF20; PC; brass chemically nickel-plated		
Materials (wetted parts)		stainless steel (1.4401 / 316); stainless steel (1.4404 / 316L); brass (2.0371); brass chemically nickel-plated; PPS; O-ring: FKM		
Process connection		threaded connection G 1 Internal thread		
Switching cycles mechanical		10 million		
Displays / operating elements				
Display	Display unit	6 x LED, green		
	Switching status	2 x LED, yellow		
	Measured values	alphanumeric display, red/green alternating indication 4-digit		
	Programming	alphanumeric display, 4-digit		
Remarks				
Remarks	<p>Use of 200 micron filtration is recommended.</p> <p>All data refer to oil with the following nominal viscosity: 68 mm<sup>2</sup>/s, 40 °C</p> <p>MW = Measured value</p> <p>MEW = Final value of the measuring range</p>			
Pack quantity	1 pcs.			
Electrical connection				
Connector: 1 x M12; coding: A; Contacts: gold-plated				



**Flow meter with fast response and display**

SBG11KL0FRKG

**Connection****OUT1:**

- Switching output Volumetric flow quantity monitoring
- Switching output Temperature monitoring
- Frequency output Volumetric flow quantity monitoring
- Frequency output Temperature monitoring
- IO-Link

**OUT2:**

- Switching output Volumetric flow quantity monitoring
- Switching output Temperature monitoring
- analog output Volumetric flow quantity monitoring
- analog output Temperature monitoring
- Colors to DIN EN 60947-5-2

Core colors :

- |      |       |
|------|-------|
| BK = | black |
| BN = | brown |
| BU = | blue  |
| WH = | white |

**Diagrams and graphs**