


Flow meter with fast response and display

SBN34IQ0FRKG



Please note the changed housing design!



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1	
Measuring range	10...600 gph	0.2...10 gpm
Process connection	threaded connection 3/4" NPT	

Application

System	gold-plated contacts
Application	for industrial applications
Media	Liquids; water; glycol solutions; Coolants
Note on media	oil 1 with viscosity: 10 mm ² /s (104 °F) oil 2 with viscosity: 46 mm ² /s (104 °F)
Medium temperature [°F]	14...212
Pressure rating [bar]	40
Pressure rating [MPa]	4
MAWP (for applications according to CRN) [bar]	40

Electrical data

Operating voltage [V]	18...30 DC; (to SELV/PELV)
Current consumption [mA]	< 50
Protection class	III
Reverse polarity protection	yes

SBN234



Flow meter with fast response and display

SBN34IQ0FRKG

Power-on delay time	[s]	< 3
Inputs / outputs		
Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1	
Outputs		
Total number of outputs		2
Output signal	switching signal; analog signal; frequency signal; IO-Link; (configurable)	
Number of digital outputs		2
Output function	normally open / closed; (configurable)	
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	150; (per output 2 x 200 (...140 °F); 2 x 250 (...104 °F))
Switching cycles (mechanical)		10 million
Number of analog outputs		1
Analog current output	[mA]	4...20
Max. load	[Ω]	500
Short-circuit protection		yes
Overload protection		yes
Frequency of the output	[Hz]	0...10000
Measuring/setting range		
Measuring range	10...600 gph	0.2...10 gpm
Display range	0...720 gph	0...12 gpm
Resolution	5 gph	0.1 gpm
Set point SP	5...600 gph	0.1...10 gpm
Reset point rP	0...595 gph	0...9.9 gpm
Frequency end point, FEP	40...600 gph	0.67...10 gpm
In steps of	5 gph	0.1 gpm
Frequency at the end point FRP	[Hz]	10...10000
Measuring dynamics		1:50
Temperature monitoring		
Measuring range	[°F]	14...212
Display range	[°F]	-26...252
Resolution	[°F]	2
Set point SP	[°F]	16...212
In steps of	[°F]	2
Frequency start point, FSP	[°F]	14...172
Frequency end point, FEP	[°F]	54...212
Frequency at the end point FRP	[Hz]	10...10000
Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)	± (4 % MW + 1 % MEW); (Q > 1 l/min; medium and operating temperature: +71,6 °F ± 4K)	
Repeatability	± 1 % MEW	

Flow meter with fast response and display

SBN34IQ0FRKG

Temperature monitoring		
Temperature drift		0,9802 °F / K
Accuracy	[K]	3 K (77 °F; Q > 1 l/min)
Reaction times		
Flow monitoring		
Response time	[s]	0.01
Damping process value dAP	[s]	0...5
Damping for the analog output dAA	[s]	0...5
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 120 (Q > 1 l/min)
Software / programming		
Parameter setting options		hysteresis / window; normally open / closed; switching logic; current output; medium selection; damping for the switching output / analog output; display can be rotated and switched off; standard unit of measurement; process value color
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9 CDV
Profiles		Smart Sensor: Process Data Variable; Device Identification
SIO mode		yes
Required master port class		A
Process data analog		2
Process data binary		2
Min. process cycle time	[ms]	5
Supported DeviceIDs	Type of operation	DeviceID
	default	567
Operating conditions		
Ambient temperature	[°F]	32...140
Note on ambient temperature		medium temperature < 176 °F medium temperature < 212 °F: 32...104 °F
Storage temperature	[°F]	5...176
Protection		IP 65; IP 67
Tests / approvals		
EMC		DIN EN 61000-6-2 DIN EN 61000-6-3
Shock resistance		DIN EN 60068-2-27
Vibration resistance		DIN EN 60068-2-6
MTTF	[years]	145
UL approval		UL approval number
Pressure equipment directive		1005 sound engineering practice; can be used for group 2 fluids; group 1 fluids on request
Mechanical data		
Weight	[g]	693

Flow meter with fast response and display

SBN34IQ0FRKG

Material	stainless steel (1.4404 / 316L); PBT+PC-GF30; PBT-GF20; PC; brass chemically nickel-plated			
Materials (wetted parts)	stainless steel (1.4401 / 316); stainless steel (1.4404 / 316L); brass (2.0371); brass chemically nickel-plated; PPS; O-ring: FKM			
Process connection	threaded connection 3/4" NPT			
Displays / operating elements				
Display	Display unit	3 x LED, green		
	Switching status	2 x LED, yellow		
	Measured values	alphanumeric display, red/green 4-digit		
	Programming	alphanumeric display, 4-digit		
Remarks				
Remarks	Use of 200 micron filtration is recommended. All data refer to water (68 °F). MW = Measured value MEW = Final value of the measuring range			
Notes	Please note the changed housing design!			
Pack quantity	1 pcs.			
Electrical connection				
Connector: 1 x M12; coding: A; Contacts: gold-plated				



Flow meter with fast response and display

SBN34IQ0FRKG

Connection



OUT1:

- Switching output Volumetric flow quantity monitoring
- Switching output Temperature monitoring
- Frequency output Volumetric flow quantity monitoring
- Frequency output Temperature monitoring
- IO-Link

OUT2:


- Switching output Volumetric flow quantity monitoring
- Switching output Temperature monitoring
- analog output Volumetric flow quantity monitoring
- analog output Temperature monitoring
- Colors to DIN EN 60947-5-2

Core colors :

BK =	black
BN =	brown
BU =	blue
WH =	white

Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity