
RC6010

Incremental encoder with solid shaft

RC-0250-I24/L2

Article no longer available - archive entry



1 reference mark
2 M3 Depth 5 mm

Product characteristics		
Resolution		250 resolution
Shaft design		solid shaft
Shaft diameter	[mm]	6
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 150
Outputs		
Electrical design		HTL
Max. current load per output	[mA]	50
Switching frequency	[kHz]	300
Type of short-circuit protection		< 60 s
Phase difference A und B	[°]	90
Measuring/setting range		
Resolution		250 resolution
Operating conditions		
Ambient temperature	[°C]	-40...100
Note on ambient temperature		firmly laid cable: -40 °C
Max. relative air humidity	[%]	98
Protection		IP 64; (on the housing: IP 67; on the shaft: IP 64)
Tests / approvals		
Shock resistance		200 g
Vibration resistance		30 g

RC6010

Incremental encoder with solid shaft

RC-0250-I24/L2

Mechanical data		
Weight	[g]	478.6
Dimensions	[mm]	Ø 58 / L = 44.6
Material		aluminum
Max. revolution, mechanical	[U/min]	16000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	6
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20


Electrical connection

Cable: 2 m, PUR; Maximum cable length: 300 m; radial, can also be used axially

brown	A
green	A inverted
grey	B
pink	B inverted
red	0 index
black	0 index inverted
blue	L+ sensor
white	0V sensor
brown/green	L+ (Up)
white/green	0V (Un)
lilac	error inverted
screen	housing

Diagrams and graphs

Pulse diagram



Direction of rotation clockwise (looking at the shaft)