Flow meter with fast response and display

SBN34IQ0FRKG



Please note the changed housing design! 27 M8x6/8 M12 14 76 141



Product characteristics					
Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1				
Measuring range	10600 gph	0.210 gpm			
Process connection	threaded connection 3/4" NPT				
Application					
System	gold-plated contacts				
Application	for industrial applications				
Media	Liquids; water; glycol solutions; Coolants				

Flow meter with fast response and display





Note on media			oil 1 with viscosity: 10 mm²/s (104 °F)	
			oil 2 with viscosity: 46 mm²/s (104 °F)	
Medium temperature	[°F]	14212		
Pressure rating	[bar]	40		
Pressure rating	[MPa]	4		
MAWP (for applications according to CRN)	[bar]	40		
Electrical data				
Operating voltage	[V]	1830 DC; (to SELV/PELV)		
Current consumption	[mA]		< 50	
Protection class		III		
Reverse polarity protection		yes		
Power-on delay time	[s]		< 3	
Inputs / outputs				
Number of inputs and output	s	Nu	mber of digital outputs: 2; Number of analog outputs: 1	
		- Nu	niber of digital outputs. 2, Number of analog outputs. 1	
Outputs Total number of outputs				
Total number of outputs			2	
Output signal		switching s	ignal; analog signal; frequency signal; IO-Link; (configurable)	
Number of digital outputs		2		
Output function			normally open / closed; (configurable)	
Max. voltage drop switching output DC	[V]	2		
Permanent current rating of switching output DC	[mA]	150; (per output 2 x 200 (140 °F); 2 x 250 (104 °F))		
Switching cycles (mechanical)		10 million		
Number of analog outputs		1		
Analog current output	[mA]	420		
Max. load	[Ω]	500		
Short-circuit protection		ves		
Overload protection		yes		
Frequency of the output	[Hz]	010000		
Measuring/setting range	. ,			
Measuring range		10600 gph	0.210 gpm	
Display range		0720 gph	012 gpm	
Resolution		5 gph	0.1 gpm	
Set point SP		5600 gph	0.110 gpm	
Reset point rP		0595 gph	09.9 gpm	
Frequency end point, FEP		40600 gph	0.6710 gpm	
In steps of		5 gph	0.1 gpm	
Frequency at the end point FRP	[Hz]	1010000		
Measuring dynamics		1:50		
Temperature monitoring				
Measuring range	[°F]	14212		
Display range	[°F]	-26252		
- opia, rango	ι']	-20202		

Flow meter with fast response and display



SBN34IQ0FRKG

Resolution	[°F]		2	
Set point SP	[°F]	16212		
In steps of	[°F]	2		
Frequency start point, FSP	[°F]	14172		
Frequency end point, FEP	[°F]	54212		
Frequency at the end point FRP	[Hz]	1010000		
Accuracy / deviations				
Flow monitoring				
Accuracy (in the measuring range)		\pm (4 % MW + 1 % MEW); (Q > 1 l/min; medium and operating temperature: +71,6 °F \pm 4K)		
Repeatability			± 1 % MEW	
Temperature monitoring				
Temperature drift			0,9802 °F / K	
Accuracy	[K]		3 K (77 °F; Q > 1 l/min)	
Reaction times				
Flow monitoring				
Response time	[s]		0.01	
Damping process value dAP	[s]	05		
Damping for the analog output dAA	[s]	05		
Temperature monitoring				
Dynamic response T05 / T09	[s]		T09 = 120 (Q > 1 l/min)	
Software / programming				
Parameter setting options		hysteresis / window; normally open / closed; switching logic; current output; medium selection; damping for the switching output / analog output; display can be rotated and switched off; standard unit of measurement; process value color		
Interfaces				
Communication interface		IO-Link		
Transmission type		COM2 (38,4 kBaud)		
IO-Link revision		1.1		
SDCI standard		IEC 61131-9 CDV		
Profiles		Smart Sensor: Process Data Variable; Device Identification		
SIO mode		yes		
Required master port class		Α		
Process data analog		2		
Process data binary		2		
Min. process cycle time	[ms]		5	
Supported DeviceIDs		Type of operation	DeviceID	
		default	567	
Operating conditions	LoL-1		20, 140	
Ambient temperature	[°F]	32140		
Note on ambient temperature		medium temperature < 176 °F medium temperature < 212 °F: 32104 °F		
Storage temperature	[°F]	5176		

Flow meter with fast response and display





Protection		IP 65; IP 67		
Tests / approvals				
EMC		DIN EN 61000-6-2		
		DIN EN 61000-6-3		
Shock resistance		DIN EN 60068-2-27	20 g (11 ms)	
Vibration resistance		DIN EN 60068-2-6	5 g (102000 Hz)	
MTTF	[years]	145		
UL approval		UL approval number	1005	
Pressure equipment directive	re e	sound engineering practice; can be used for group 2 fluids; group 1 fluids on request		
Mechanical data				
Weight	[g]	693		
Material		stainless steel (1.4404 / 316L); PBT+PC-GF30;		
		PBT-GF20; PC; brass chemically nickel-plated		
Materials (wetted parts)		stainless steel (1.4401 / 316); stainless steel (1.4404 / 316L); brass (2.0371); brass chemically nickel-plated; PPS; O-ring: FKM		
Process connection		threaded connection 3/4" NPT		
Displays / operating eleme	ents			
Display		Display unit	3 x LED, green	
		Switching status	2 x LED, yellow	
		Measured values	alphanumeric display, red/green 4-digit	
		Programming	alphanumeric display, 4-digit	
Remarks				
Remarks		Use of 200 micron filtration is recommended.		
		All data refer to water (68 °F).		
		MW = Measured value		
		MEW = Final value of the measuring range		
Notes		Please note the changed housing design!		
Pack quantity		1 pcs.		
Electrical compaction				

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated




Flow meter with fast response and display

SBN34IQ0FRKG

Connection





OUT1:

- Switching output Volumetric flow quantity monitoring

- Switching output Temperature monitoring

- Frequency output Volumetric flow quantity monitoring

- Frequency output Temperature monitoring

- IO-Link

OUT2:

- Switching output Volumetric flow quantity monitoring

- Switching output Temperature monitoring

- analog output Volumetric flow quantity monitoring

- analog output Temperature monitoring

Colors to DIN EN 60947-5-2

Core colors:

 BK =
 black


 BN =
 brown

 BU =
 blue

 WH =
 white

Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity