


SBG232



Flow meter with fast response and display

SBG12IF0FRKG

Please note the changed housing design!



CE CRN cUL us IO-Link
LISTED

Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1
Measuring range	0.3...15 l/min 0.018...0.9 m³/h
Process connection	threaded connection G 1/2
Application	
System	gold-plated contacts
Application	for industrial applications
Media	Liquids; water; glycol solutions; Coolants
Note on media	oil 1 with viscosity: 10 mm²/s (40 °C) oil 2 with viscosity: 46 mm²/s (40 °C)
Medium temperature [°C]	-10...100

SBG232



Flow meter with fast response and display

SBG12IF0FRKG

Min. bursting pressure	[bar]	160
Pressure rating	[bar]	40
Pressure rating	[MPa]	4
MAWP (for applications according to CRN)	[bar]	40
Electrical data		
Operating voltage	[V]	18...30 DC; (to SELV/PELV)
Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	< 3
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2; Number of analog outputs: 1
Outputs		
Total number of outputs		2
Output signal		switching signal; analog signal; frequency signal; IO-Link; (configurable)
Number of digital outputs		2
Output function		normally open / closed; (configurable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	150; (per output 2 x 200 (...60 °C); 2 x 250 (...40 °C))
Switching cycles (mechanical)		10 million
Number of analog outputs		1
Analog current output	[mA]	4...20
Max. load	[Ω]	500
Short-circuit protection		yes
Overload protection		yes
Frequency of the output	[Hz]	0...10000
Measuring/setting range		
Measuring range		0.3...15 l/min 0.018...0.9 m³/h
Display range		0...18 l/min 0...1.08 m³/h
Resolution		0.05 l/min 0.005 m³/h
Set point SP		0.1...15 l/min 0.005...0.9 m³/h
Reset point rP		0...14.9 l/min 0...0.895 m³/h
Frequency end point, FEP		1...15 l/min 0.06...0.9 m³/h
In steps of		0.05 l/min 0.005 m³/h
Frequency at the end point FRP	[Hz]	10...10000
Measuring dynamics		1:50
Temperature monitoring		
Measuring range	[°C]	-10...100
Display range	[°C]	-32...122
Resolution	[°C]	1
Set point SP	[°C]	-9...100

SBG232



Flow meter with fast response and display

SBG12IF0FRKG

Reset point rP	[°C]	-10...99
In steps of	[°C]	1
Frequency start point, FSP	[°C]	-10...78
Frequency end point, FEP	[°C]	12...100
Frequency at the end point FRP	[Hz]	10...10000

Accuracy / deviations

Flow monitoring	
Accuracy (in the measuring range)	± (4 % MW + 1 % MEW); (Q > 0,3 l/min; medium and operating temperature: +22 °C ± 4K)
Repeatability	± 1 % MEW
Temperature monitoring	
Temperature drift	0,029 °C / K
Accuracy	[K] 3 K (25°C; Q > 1 l/min)

Reaction times

Flow monitoring	
Response time	[s] 0.01
Damping process value dAP	[s] 0...5
Damping for the analog output dAA	[s] 0...5
Temperature monitoring	
Dynamic response T05 / T09	[s] T09 = 120 (Q > 1 l/min)

Software / programming

Parameter setting options	hysteresis / window; normally open / closed; switching logic; current/frequency output; medium selection; damping for the switching output / analog output; display can be rotated and switched off; standard unit of measurement; process value color
---------------------------	--

Interfaces

Communication interface	IO-Link				
Transmission type	COM2 (38,4 kBaud)				
IO-Link revision	1.1				
SDCI standard	IEC 61131-9 CDV				
Profiles	Smart Sensor: Process Data Variable; Device Identification				
SIO mode	yes				
Required master port class	A				
Process data analog	2				
Process data binary	2				
Min. process cycle time	[ms] 5				
Supported DeviceIDs	<table border="1"><thead><tr><th>Type of operation</th><th>DeviceID</th></tr></thead><tbody><tr><td>default</td><td>560</td></tr></tbody></table>	Type of operation	DeviceID	default	560
Type of operation	DeviceID				
default	560				

Operating conditions

Ambient temperature	[°C]	0...60
Note on ambient temperature		medium temperature < 80 °C
		medium temperature < 100 °C: 0...40 °C
Storage temperature	[°C]	-15...80
Protection		IP 65; IP 67

SBG232



Flow meter with fast response and display

SBG12IF0FRKG

Tests / approvals				
EMC	DIN EN 61000-6-2			
	DIN EN 61000-6-3			
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)		
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)		
MTTF [years]		145		
UL approval	UL approval number	I005		
Pressure equipment directive	sound engineering practice; can be used for group 2 fluids; group 1 fluids on request			
Mechanical data				
Weight [g]	750			
Material	stainless steel (1.4404 / 316L); PBT+PC-GF30; PBT-GF20; PC; brass chemically nickel-plated			
Materials (wetted parts)	stainless steel (1.4401 / 316); stainless steel (1.4404 / 316L); brass (2.0371); brass chemically nickel-plated; PPS; O-ring: FKM			
Process connection	threaded connection G 1/2			
Displays / operating elements				
Display	Display unit	3 x LED, green		
	Switching status	2 x LED, yellow		
	Measured values	alphanumeric display, red/green 4-digit		
	Programming	alphanumeric display, 4-digit		
Remarks				
Remarks	Use of 200 micron filtration is recommended. All data refer to water (20 °C). MW = Measured value MEW = Final value of the measuring range			
Notes	Please note the changed housing design!			
Pack quantity	1 pcs.			
Electrical connection				
Connector: 1 x M12; coding: A; Contacts: gold-plated				



Flow meter with fast response and display

SBG12IF0FRKG

Connection



OUT1:

- Switching output Volumetric flow quantity monitoring
- Switching output Temperature monitoring
- Frequency output Volumetric flow quantity monitoring
- Frequency output Temperature monitoring
- IO-Link

OUT2:


- Switching output Volumetric flow quantity monitoring
- Switching output Temperature monitoring
- analog output Volumetric flow quantity monitoring
- analog output Temperature monitoring
- Colors to DIN EN 60947-5-2

Core colors :

BK =	black
BN =	brown
BU =	blue
WH =	white

Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity