
SBU624

Flow transmitters with fast response time

SBU12DI040KG/US







Product characteristics				
Measuring range	[l/min]	0.350		
Process connection		G 1/2		
Application				
Application		Machine tools; Internal cooling of drill		
Media		Liquids; water; glycol solutions; Coolants		
Medium temperature	[°C]	060		
Pressure rating	[bar]	200		
Pressure rating	[MPa]	20		
Electrical data				
Operating voltage tolerance	[%]	-1510		
Operating voltage	[V]	24 DC; (to SELV/PELV)		
Current consumption	[mA]	10		
Protection class		III		
Reverse polarity protection		yes		
Outputs				
Output signal		analog signal		
Analog voltage output	[V]	0.510		
Min. load resistance	[Ω]	10000		
Short-circuit protection		yes		
Overload protection		yes		

SBU624

Flow transmitters with fast response time





Measuring/setting range					
Measuring range	[l/min]	0.350			
Flow range	[l/min]	75			
Accuracy / deviations					
Repeatability		1			
[% of the final value]		1			
Measuring error		±5			
[% of the final value]					
Reaction times	r-1				
Response time	[s]	< 0.01			
Operating conditions					
Ambient temperature	[°C]	060			
Storage temperature	[°C]	-1580			
Protection		IP 65; IP 67			
Tests / approvals					
EMC		DIN EN 61000-6-2			
Shock resistance		DIN EN 61000-6-3 DIN EN 60068-2-27	20 g (11 ms)		
Vibration resistance		DIN EN 60068-2-6	5 g (102000 Hz)		
MTTF	[years]	1	5.78		
Mechanical data					
Weight	[g]	737			
Material		aluminum anodized; PA			
Materials (wetted parts)		stainless steel (1.4401 / 316); brass; aluminum anodized; PU; O-ring: FKM			
Process connection		G 1/2			
Switching cycles mechai	cycles mechanical		10 million		
Accessories					
Items supplied		sealing plug			
Remarks					
Remarks		Temperature changes affect the specified standard settings for coolants.			
		For oils, the settings are influenced by temperature and viscosity.			
		Recommendation Use 200 micron filtration			
Pack quantity		All data refer to coolants (20 °C). 1 pcs.			
Electrical connection			pos.		
Connector: 1 x M12; coding: A					


SBU624

Flow transmitters with fast response time





Connection



Colors to DIN EN 60947-5-2

Core colors :

BN = brown BU = blue WH = white

Diagrams and graphs

