


#### Flow sensor with fast response time



SBY34BF0BPKG/US



# 

Product characteristics		
Number of inputs and outputs		Number of digital outputs: 1
Process connection		Rp 3/4
Application		
Media		Liquids; water; glycol solutions; Coolants
Medium temperature	[°C]	085
Pressure rating	[bar]	40
Pressure rating	[MPa]	4
Electrical data		
Operating voltage	[V]	1030 DC; (to SELV/PELV)
Current consumption	[mA]	< 15
Protection class		III
Reverse polarity protection	n	yes

## **SBY334**

#### Flow sensor with fast response time

SBY34BF0BPKG/US




Inputs / outputs				
Number of inputs and outputs	Number of digital outputs: 1			
Outputs				
Total number of outputs	1			
Output signal	switching signal			
Electrical design	PNP			
Number of digital outputs	1			
Output function	normally open			
Max. voltage drop switching [V] output DC	2.5			
Permanent current rating of [mA] switching output DC	100			
Short-circuit protection	yes			
Overload protection	yes			
Measuring/setting range				
Setting range [l/min]	250			
Accuracy / deviations				
Repeatability	1			
[% of the final value]				
Hysteresis [l/min]	13			
Measuring error	± 5			
[% of the final value]				
Reaction times				
Response time [s]	< 0.01			
Operating conditions				
Ambient temperature [°C]				
Storage temperature [°C]				
Protection	IP 65; IP 67			
Tests / approvals				
EMC	DIN EN 61000-6-2			
Chaole registeres	DIN EN 61000-6-3			
Shock resistance Vibration resistance	DIN EN 60068-2-27 20 g (11 ms)   DIN EN 60068-2-6 5 g (102000 Hz)			
MTTF [years]				
Mechanical data				
Weight [g]	476.5			
Material	brass chemically nickel-plated; PP; aluminum anodized; PA			
Materials (wetted parts)	stainless steel (1.4310 / 301); stainless steel (1.4301 / 304); PBT;			
	brass chemically nickel-plated; PP; PPS; Polyolefin; O-ring: FKM			
Process connection	Rp 3/4			
Switching cycles mechanical	10 million			
Displays / operating elements				
Display	Switching status 4 x LED, yellow			

## **SBY334**

### Flow sensor with fast response time

SBY34BF0BPKG/US

Accessories	
Items supplied	Allen key
Remarks	
Remarks	Caution Do not turn the cap beyond the maximum value of the setting range.
	All data refer to water (20 °C).
Notes	Please note the changed housing design!
Pack quantity	1 pcs.
Electrical connection	
Connector: 1 x M12; coding: A	
2 3 4	
Connection	
	<b>1</b> +



## **SBY334**

#### Flow sensor with fast response time

SBY34BF0BPKG/US



