


Flow sensor with fast response time



SBY32BF0BPKG/US



Product characteristics			
Number of inputs and outputs		Number of digital outputs: 1	
Process connection		Rp 1 1/2	
Application			
Media		Liquids; water; glycol solutions; Coolants	
Medium temperature	[°C]	085	
Pressure rating	[bar]	25	
Pressure rating	[MPa]	2.5	

SBY357

Flow sensor with fast response time

SBY32BF0BPKG/US

Electrical data				
Operating voltage	[V]	1030 DC; (to SELV/PELV)		
Current consumption	[mA]	<15		
Protection class				
Reverse polarity protection		yes		
Inputs / outputs				
Number of inputs and outputs	;	Number of digital outputs: 1		
Outputs				
Total number of outputs		1		
Output signal		switching signal		
Electrical design		PNP		
Number of digital outputs		1		
Output function		normally open		
Max. voltage drop switching	[V]			
output DC		2.5		
Permanent current rating of switching output DC	[mA]	100		
Short-circuit protection		yes		
Overload protection		yes		
Measuring/setting range				
Setting range	[l/min]	20200		
Accuracy / deviations				
Repeatability		1		
[% of the final value]		1		
Hysteresis	[l/min]	510		
Measuring error		± 5		
[% of the final	valuej			
Reaction times		. 0.01		
Response time	[s]	< 0.01		
Operating conditions	50.01			
Ambient temperature	[°C]	060		
Storage temperature	[°C]	-1580		
Protection		IP 65; IP 67		
Tests / approvals	1			
EMC		DIN EN 61000-6-2 DIN EN 61000-6-3		
Shock resistance		DIN EN 61000-6-3 DIN EN 60068-2-27 20 g (11 ms)		
Vibration resistance		DIN EN 60068-2-6 5 g (11 ms)		
	[years]	3318		
Mechanical data				
Weight	[g]	2141.8		
Material		brass chemically nickel-plated; PP; aluminum anodized; PA		
Materials (wetted parts)		stainless steel (1.4310 / 301); stainless steel (1.4301 / 304); PBT; brass chemically nickel-plated; PP; PPS; spacer: POM; Polyolefin; O-ring: FKM		

SBY357

Flow sensor with fast response time


SBY32BF0BPKG/US



Process connection	Rp 1 1/2					
Switching cycles mechanical	10 million					
Displays / operating elements						
Display	Switching status	4 x LED, yellow				
Accessories						
Items supplied	Allen key					
Remarks						
Remarks	Caution Do not turn t	he cap beyond the maximum value of the setting range.				
		All data refer to water (20 °C).				
Notes	Please note the changed housing design!					
Pack quantity		1 pcs.				
Electrical connection						
Connector: 1 x M12; coding: A						

Connection

2 3



SBY357

Flow sensor with fast response time

SBY32BF0BPKG/US

