

**Product characteristics**

Measuring range	1...50 l/min	0.06...3 m³/h	16...793 gph	0.26...13.2 gpm
Process connection	threaded connection G 1/2 Internal thread			

**Application**

System	gold-plated contacts
Media	Liquids; water; glycol solutions; Coolants
Medium temperature [°C]	-10...100
Pressure rating [bar]	200
Pressure rating [MPa]	20

**Electrical data**

Operating voltage [V]	18...30 DC; (to SELV/PELV)
Current consumption [mA]	< 50
Protection class	III
Reverse polarity protection	yes

# SBZ224



## Flow meter with fast response and display

SBZ12IIBFRKG

Power-on delay time	[s]	< 3		
<b>Outputs</b>				
Total number of outputs		2		
Output signal		switching signal; analog signal; frequency signal; IO-Link		
Output function		normally open / closed; (configurable)		
Max. voltage drop switching output DC	[V]	2		
Max. current load per output	[mA]	150; (200: ...60 °C; Ambient temperature; 250: ...40 °C; Ambient temperature)		
Analog current output	[mA]	4...20		
Max. load	[Ω]	500		
Short-circuit protection		yes		
Overload protection		yes		
Frequency of the output	[Hz]	0...10000		
<b>Measuring/setting range</b>				
Measuring range	1...50 l/min	0.06...3 m³/h	16...793 gph	0.26...13.2 gpm
Display range	0...60 l/min	0...3.6 m³/h	0...951 gph	0...15.86 gpm
Resolution	0.01 l/min	0.001 m³/h	1 gph	0.01 gpm
Set point SP	0.35...50 l/min	0.02...3 m³/h	5...793 gph	0.08...13.2 gpm
Reset point rP	0...49.65 l/min	0...2.98 m³/h	0...787 gph	0...13.12 gpm
Frequency end point, FEP	3.35...50 l/min	0.2...3 m³/h	53...793 gph	0.88...13.2 gpm
In steps of	0.05 l/min	0.005 m³/h	1 gph	0.02 gpm
Frequency at the end point FRP	[Hz]	10...10000		
In steps of	[Hz]	10		
Measuring dynamics		1:50		
<b>Temperature monitoring</b>				
Measuring range	-10...100 °C		14...212 °F	
Display range	-32...122 °C		-25.6...251.6 °F	
Resolution	0.1 °C		0.1 °F	
Set point SP	-9.3...100 °C		15.2...212 °F	
Reset point rP	-10...99.3 °C		14...210.8 °F	
In steps of	0.1 °C		0.2 °F	
Frequency start point, FSP	-10...78 °C		14...172.4 °F	
Frequency end point, FEP	12...100 °C		53.6...212 °F	
Frequency at the end point FRP	[Hz]	10...10000		
In steps of	[Hz]	10		
<b>Accuracy / deviations</b>				
Flow monitoring				
Accuracy (in the measuring range)		± (4 % MW + 1 % MEW); (Q > 1 l/min; medium and operating temperature: + 22 °C ± 4K; Mounting orientation upright)		
Repeatability		± 1 % MEW		
Temperature monitoring				
Temperature drift		0,029 °C / K		
Accuracy	[K]	3 K (25 °C; Q > 1 l/min)		

# SBZ224



## Flow meter with fast response and display

SBZ12IIBFRKG

Reaction times		
Flow monitoring		
Response time	[s]	0.01
Damping process value dAP	[s]	0...5
In steps of	[s]	0.1
Damping for the analog output dAA	[s]	0...5
In steps of	[s]	0.1
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 120 (Q > 1 l/min)
Software / programming		
Parameter setting options	hysteresis / window; normally open / closed; switching logic; current/frequency output; damping for the switching output / analog output; display can be rotated and switched off; standard unit of measurement; process value color; calibration factor	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis	
SIO mode	yes	
Required master port class	A	
Process data analog	2	
Process data binary	2	
Min. process cycle time	[ms]	3.2
Supported DeviceIDs	Type of operation	DeviceID
	default	1447
Operating conditions		
Ambient temperature	[°C]	0...60
Note on ambient temperature	medium temperature < 80 °C medium temperature < 100 °C: 0...40 °C	
Storage temperature	[°C]	-15...80
Protection	IP 65; IP 67	
Tests / approvals		
EMC	DIN EN 61000-6-2 DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[years]	170
Pressure equipment directive	sound engineering practice	
Mechanical data		
Weight	[g]	1734.3
Dimensions	[mm]	175.5 x 39 x 59
Material	stainless steel (1.4404 / 316L); PBT+PC-GF30; PBT-GF20; PC	
Materials (wetted parts)	stainless steel (1.4401 / 316); stainless steel (1.4404 / 316L); O-ring: FKM	

# SBZ224



## Flow meter with fast response and display

SBZ12IIBFRKG

Process connection	threaded connection G 1/2 Internal thread
Switching cycles mechanical	10 million
<b>Displays / operating elements</b>	
Display	Display unit 6 x LED, green
	Switching status 2 x LED, yellow
	Measured values alphanumeric display, red/green alternating indication 4-digit
	Programming alphanumeric display, 4-digit
<b>Remarks</b>	
Remarks	Use of 200 micron filtration is recommended. All data refer to water (20 °C). Mounting orientation upright MW = Measured value MEW = Final value of the measuring range
Pack quantity	1 pcs.
<b>Electrical connection</b>	
Connector: 1 x M12; coding: A; Contacts: gold-plated	
	

**Flow meter with fast response and display**

SBZ12IIBFRKG

**Connection****OUT1:**

- Switching output Volumetric flow quantity monitoring
- Switching output Temperature monitoring
- Frequency output Volumetric flow quantity monitoring
- Frequency output Temperature monitoring
- IO-Link

**OUT2:**

- Switching output Volumetric flow quantity monitoring
- Switching output Temperature monitoring
- analog output Volumetric flow quantity monitoring
- analog output Temperature monitoring
- Colors to DIN EN 60947-5-2

Core colors :

- |      |       |
|------|-------|
| BK = | black |
| BN = | brown |
| BU = | blue  |
| WH = | white |

**Diagrams and graphs**