
# SF120A

### Flow sensor for connection to an evaluation unit



SFM12ABB/US/2G



Product characteristic	cs	
Probe length L	[mm]	12
Process connection		M12 x 1
Application		
Media		Liquids; Gases
Medium temperature	[°C]	-2070
Pressure rating	[bar]	30
Liquids		
Medium temperature	[°C]	-2070
Gases		
Medium temperature	[°C]	-2070
Electrical data		
Connection to control monitor		VS2000 Exi (PTB 01 ATEX 2075)
Measuring/setting ran	ige	
Probe length L	[mm]	12
Liquids		
Setting range	[cm/s]	3300
Greatest sensitivity	[cm/s]	360
Gases		
Setting range	[cm/s]	2002000
Greatest sensitivity	[cm/s]	200800
Accuracy / deviations	i	
Max. temperature gradient of[K/min] medium		15
Reaction times		
Response time	[S]	110
Liquids		
	[0]	110
Response time	[s]	110
Response time Gases	[5]	110

## SF120A

#### Flow sensor for connection to an evaluation unit



SFM12ABB/US/2G

3

Operating conditions	[20]				
Ambient temperature	[°C]	-2070			
Protection		IP 67			
Tests / approvals					
Approval		DMT 03 ATEX E091; IECEX BVS 06.0007			
ATEX marking		$\langle \epsilon_x \rangle$ II 2G Ex ia IIC T4 Gb			
Shock resistance		DIN IEC 68-2-27 40 g (11 ms)			
Vibration resistance		DIN IEC 68-2-6 10 g (552000 Hz)			
MTTF	[years]	8648			
Safety classification					
Max. internal capacitance	[nF]	0.4			
Max. internal inductance	[µH]	2			
Temperature class		Τ4			
Mechanical data					
Weight	[g]	111.5			
Housing		Threaded type			
Dimensions	[mm]	M12 x 1			
Thread designation		M12 x 1			
Material		stainless steel (1.4404 / 316L)			
Materials (wetted parts)		stainless steel (1.4404 / 316L)			
Process connection		M12 x 1			
Installation length EL	[mm]	27			
Remarks					
Remarks		In principle, the type test according to 94/9/EC (ATEX) only			
		takes atmospheric conditions into account (0.81.1 bar).			
		For pressures outside this range use must be assessed and approved by the user.			
Pack quantity		Adhere to the operating instructions and the type test certificate.			
		1 pcs.			
Electrical connection					
Connector: 1 x M12; coding: A; Maximum cable length: 100 m					
2 1					


## SF120A

### Flow sensor for connection to an evaluation unit



SFM12ABB/US/2G

#### Connection



	Core color
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey