
# SF3405

## Flow sensor for connection to an evaluation unit







# CE CA

Duadwat abayastayiatian			
Product characteristics Probe length L	[mm]		20
	[mm]	30	
Process connection		G 1/2 exte	ernal thread
Application			
Media			ressive media
Medium temperature	[°C]	5.	70
Pressure rating	[bar]		30
Liquids			
Medium temperature	[°C]	5	70
Electrical data			
Connection to control monitor		VS:	3000
Measuring/setting range			
Probe length L	[mm]		30
Liquids			
Setting range	[cm/s]	3.	60
Greatest sensitivity	[cm/s]	3.	40
Accuracy / deviations			
Max. temperature gradient of[K/min] medium			7
Reaction times			
Response time	[s]	2	20
Liquids			
Response time	[s]	2.	20
Operating conditions			
Protection		IP	9 67
Tests / approvals			
Shock resistance		DIN IEC 68-2-27	40 g (11 ms)
Vibration resistance		DIN IEC 68-2-6	10 g (552000 Hz)
MTTF	[years]	82	213

# SF3405

#### Flow sensor for connection to an evaluation unit



SFR12XBK/US-100

Mechanical data				
Weight	[g]	55		
Housing		Threaded type		
Material		ceramics (99.7 % Al2O3)		
Materials (wetted parts)		ceramics (99.7 % Al2O3)		
Process connection		G 1/2 external thread		
Installation length EL	[mm]	45		
Accessories				


Accessories		
Items supplied	supplied sealings: 1, PTFE	
Remarks		
Remarks	For sealing use the supplied PTFE packing washer.	
Pack quantity	1 pcs.	

## Electrical connection

Connector: 1 x M12; coding: A; Maximum cable length: 100 m



#### Connection



	Core colors :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey