
## SF3410

#### Flow sensor for connection to an evaluation unit



SFR12XBK/6M



# CE CA

Product characteristics	\$		
Probe length L	[mm]	30	
Process connection		G 1/2 external thread	
Application			
Media		Liquids; aggressive media	
Medium temperature	[°C]	570	
Pressure rating	[bar]	30	
Liquids			
Medium temperature	[°C]	570	
Electrical data			
Connection to control mo	onitor	VS3000	
Measuring/setting rang	le		
Probe length L	[mm]	30	
Liquids			
Setting range	[cm/s]	360	
Greatest sensitivity	[cm/s]	340	
Accuracy / deviations			
Max. temperature gradient of[K/min] medium		7	
Reaction times			
Response time	[S]	220	
Liquids			
Response time	[S]	220	
Operating conditions			
Protection		IP 67	
Tests / approvals			
Shock resistance		DIN IEC 68-2-27 40 g (11 ms)	
Vibration resistance		DIN IEC 68-2-6 10 g (552000 Hz)	
MTTF	[years]	8213	

## SF3410

### Flow sensor for connection to an evaluation unit



SFR12XBK/6M

Mechanical data		
Weight	[g]	389.5
Housing		Threaded type
Material		ceramics (99.7 % Al2O3)
Materials (wetted parts)		ceramics (99.7 % Al2O3)
Process connection		G 1/2 external thread
Installation length EL	[mm]	45
Accessories		
Items supplied		sealings: 1, PTFE
Remarks		
Remarks		For sealing use the supplied PTFE packing washer.
Pack quantity		1 pcs.
Electrical connection		
Cable: 6 m, PUR; Maximun	n cable lenç	gth: 100 m; 5 x 0.34 mm², PVC
Connection		
		WH BU BN BK GY

	Core colors :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey