

SF3004




Flow sensor for connection to an evaluation unit

SFR12ABA/US-100

Article no longer available - archive entry

Alternative articles: SF5200 or SF5201

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Process connection G 1/2 external thread

Application

Application high temperature

Media Liquids; Gases

Medium temperature [°C] -25...80

Pressure rating [bar] 30

Liquids

Application high temperature

Medium temperature [°C] -25...80

Gases

Medium temperature [°C] -25...80

Electrical data

Connection to control monitor VS 0200

Measuring/setting range

Liquids

Setting range [cm/s] 3...300

Greatest sensitivity [cm/s] 3...60

Gases

Setting range [cm/s] 200...2000

Greatest sensitivity [cm/s] 200...800

Accuracy / deviations

Max. temperature gradient of [K/min] medium 15

Reaction times

Response time [s] 1...10

Liquids

Response time [s] 1...10

SF3004




Flow sensor for connection to an evaluation unit


SFR12ABA/US-100

Gases		
Response time	[s]	1...10
Operating conditions		
Protection		IP 67
Mechanical data		
Housing		Threaded type
Material		stainless steel (1.4305 / 303)
Materials (wetted parts)		stainless steel (1.4305 / 303)
Process connection		G 1/2 external thread
Accessories		
Items supplied		sealings: 2 x AMF 30
Remarks		
Pack quantity		1 pcs.
Electrical connection		

Connector: 1 x M12; coding: A; Maximum cable length: 100 m



Connection



	Core colors :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey