

# SF3005




## Flow sensor for connection to an evaluation unit

SFR12ADB

Article no longer available - archive entry

Alternative articles: SF5350 + E40096

When selecting an alternative article and accessories please note that technical data may differ!



### Product characteristics

Process connection	G 1/2 external thread
--------------------	-----------------------

### Application

Application	high pressure
Media	Liquids; Gases
Medium temperature [°C]	-25...80
Pressure rating [bar]	300

### Liquids

Application	high pressure
Medium temperature [°C]	-25...80

### Gases

Medium temperature [°C]	-25...80
-------------------------	----------

### Electrical data

Connection to control monitor	VS 0200
-------------------------------	---------

### Measuring/setting range

#### Liquids

Setting range [cm/s]	3...300
Greatest sensitivity [cm/s]	3...60

#### Gases

Setting range [cm/s]	200...2000
Greatest sensitivity [cm/s]	200...800

### Accuracy / deviations

Max. temperature gradient of [K/min] medium	15
---	----

### Reaction times

Response time [s]	1...10
-------------------	--------

#### Liquids

Response time [s]	1...10
-------------------	--------


# SF3005



## Flow sensor for connection to an evaluation unit

SFR12ADB

Gases		
Response time	[s]	1...10
Operating conditions		
Protection		IP 67
Tests / approvals		
Shock resistance	DIN IEC 68-2-27	40 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	10 g (55...2000 Hz)
Mechanical data		
Housing		Threaded type
Material		stainless steel (1.4571/316Ti )
Materials (wetted parts)		stainless steel (1.4571/316Ti )
Process connection		G 1/2 external thread
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PUR; Maximum cable length: 100 m; 5 x 0.34 mm², PVC		
Connection		



Core colors :	
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey