
SF311A

Flow sensor for connection to an evaluation unit









Product characteristics	6	
Probe length L	[mm]	12
Process connection		G 1/2 external thread
Application		
Media		Liquids; Gases
Medium temperature	[°C]	-2060
Pressure rating	[bar]	300
Liquids		
Medium temperature	[°C]	-2060
Gases		
Medium temperature	[°C]	-2060
Electrical data		
Connection to control monitor		VS2000 Exi (PTB 01 ATEX 2075)
Measuring/setting rang	je	
Probe length L	[mm]	12
Liquids		
Setting range	[cm/s]	3300
Greatest sensitivity	[cm/s]	360
Gases		
Setting range	[cm/s]	2002000
Greatest sensitivity	[cm/s]	200800
Accuracy / deviations		
Max. temperature gradient of[K/min] medium		15
Reaction times		
Response time	[s]	110
Liquids		
Response time	[s]	110
Gases		
Response time	[s]	110

SF311A

Flow sensor for connection to an evaluation unit



SFR12ADB/1/2G /6M

Operating conditions		
Ambient temperature	[°C]	-2060
Storage temperature	[°C]	-2085
Protection		IP 67
Tests / approvals		
Approval		DMT 03 ATEX E 090 X; TIIS TC17434; IECEx BVS 11.0017 X
ATEX marking		⟨£x⟩ II 1/2G Ex ia IIC T4 Ga/Gb4
Shock resistance		DIN IEC 68-2-27 40 g (11 ms)
Vibration resistance		DIN IEC 68-2-6 10 g (552000 Hz)
MTTF	[years]	8648
Safety classification		
Max. internal capacitance	[nF]	1.2
Max. internal inductance	[μH]	6
Temperature class		T4
Mechanical data		
Weight	[g]	467
Housing		Threaded type
Material		stainless steel (1.4404 / 316L)
Materials (wetted parts)		stainless steel (1.4404 / 316L)
Process connection		G 1/2 external thread
Installation length EL	[mm]	45
Remarks		
Remarks		In principle, the type test according to 94/9/EC (ATEX) only takes atmospheric conditions into account (0.81.1 bar).
		For pressures outside this range use must be assessed and approved by the user.
		Adhere to the operating instructions and the type test certificate.
Pack quantity		1 pcs.

SF311A

Flow sensor for connection to an evaluation unit






Electrical connection

Cable: 6 m, TPE-S; Maximum cable length: 100 m; 5 x 0.34 mm²

Connection



Core colors:

 BN =
 brown

 BU =
 blue

 BK =
 black

 WH =
 white

 GY =
 grey