
SF5200

Flow sensor for connection to an evaluation unit

SFD10ADB /US-100







Product characteristics	S			
Probe length L	[mm]	45		
Process connection		M18 x 1,5 Internal thread		
Application				
Application			high ter	mperature
Media			Liquids	s; Gases
Medium temperature	[°C]		-25	580
Pressure rating	[bar]		3	300
Electrical data				
Connection to control monitor		VS3000		
Measuring/setting rang	e			
Probe length L	[mm]	45		
Liquids				
Setting range	[cm/s]	3300		
Greatest sensitivity	[cm/s]	360		
Gases				
Setting range	[cm/s]	2003000		
Greatest sensitivity	[cm/s]	200800		
Accuracy / deviations				
Max. temperature gradient of[K/min] medium		300		
Reaction times				
Response time	[s]		1.	10
Operating conditions				
Protection		IP 67		
Tests / approvals				
Shock resistance		DIN IEC 68-2-27		40 g (11 ms)
Vibration resistance		DIN IEC 68-2-6		10 g (552000 Hz)
MTTF	[years]	8213		

SF5200

Flow sensor for connection to an evaluation unit





Mechanical data				
Weight	[g]	88.5		
Housing		for adapter		
Dimensions	[mm]	M18 x 1.5		
Thread designation		M18 x 1.5		
Material		stainless steel (1.4404 / 316L)		
Materials (wetted parts)		stainless steel (1.4404 / 316L); O-ring: FKM 80 Shore A		
Process connection		M18 x 1,5 Internal thread		


Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Maximum cable length: 100 m



Connection



Core colors :

BN = brown

BU = blue

BK = black

WH = white

GY = grey