
SF5350

Flow sensor for connection to an evaluation unit

SFD10ADB /6M







Product characteristic			45	
Probe length L	[mm]		45	
Process connection			M18 x 1,5 Internal thread	
Application				
Application			high temperature	
Media			Liquids; Gases	
Medium temperature	[°C]		-2580	
Pressure rating	[bar]		300	
Electrical data				
Connection to control m	onitor	VS3000		
Measuring/setting ran	ge			
Probe length L	[mm]		45	
Liquids				
Setting range	[cm/s]		3300	
Greatest sensitivity	[cm/s]		360	
Gases				
Setting range	[cm/s]		2003000	
Greatest sensitivity	[cm/s]	200800		
Accuracy / deviations				
Max. temperature gradient of[K/min]		300		
medium				
Reaction times				
Response time	[s]		110	
Operating conditions				
Protection		IP 67		
Tests / approvals				
Shock resistance		DIN IEC 68-2-27	40 g (11 ms)	
Vibration resistance		DIN IEC 68-2-6	10 g (552000 Hz)	
MTTF	[years]		8213	

SF5350

Flow sensor for connection to an evaluation unit



SFD10ADB /6M


Mechanical data				
Weight	[g]	413.5		
Housing		for adapter		
Dimensions	[mm]	M18 x 1.5		
Thread designation		M18 x 1.5		
Material		stainless steel (1.4404 / 316L)		
Materials (wetted parts)		stainless steel (1.4404 / 316L); O-ring: FKM 80 Shore A		
Process connection		M18 x 1,5 Internal thread		

Remarks Pack quantity 1 pcs.

Electrical connection

Cable: 6 m, PUR; Maximum cable length: 100 m; 5 x 0.34 mm²

Connection



	Core colors :	
BN =	brown	
BU =	blue	
BK =	black	
WH =	white	
GY =	grey	