


# SM8400

## Magnetic-inductive flow meter

SMK11GGXFRKG/US-100



### Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1
Measuring range	0.2...100 l/min   0.01...6 m³/h
Process connection	threaded connection Rc 1 Internal thread DN25

### Application

System	gold-plated contacts
Application	Totalizer function; for industrial applications
Media	Conductive liquids; water; water-based media
Note on media	conductivity: $\geq 20 \mu\text{S/cm}$ viscosity: $< 70 \text{ mm}^2/\text{s}$ (40 °C)
Medium temperature [°C]	-10...70
Pressure rating [bar]	16
Pressure rating [MPa]	1.6

### Electrical data

Operating voltage [V]	18...30 DC; (to SELV/PELV)
Current consumption [mA]	95; (24 V)
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	5

### Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1
<b>Inputs</b>	
Inputs	counter reset
<b>Outputs</b>	
Total number of outputs	2
Output signal	switching signal; analog signal; pulse signal; IO-Link; (configurable)

# SM8400



## Magnetic-inductive flow meter

SMK11GGXFRKG/US-100

Electrical design		
Number of digital outputs		PNP/NPN
Output function		2
Max. voltage drop switching output DC	[V]	normally open / closed; (configurable)
Permanent current rating of switching output DC	[mA]	2
Number of analog outputs		200
Analog current output	[mA]	1
Max. load	[Ω]	4...20; (scalable)
Analog voltage output	[V]	500
Min. load resistance	[Ω]	0...10; (scalable)
Pulse output		2000
Short-circuit protection		flow rate meter
Type of short-circuit protection		yes
Overload protection		yes (non-latching)
Overload protection		yes
Measuring/setting range		
Measuring range	0.2...100 l/min	0.01...6 m³/h
Display range	-120...120 l/min	-7.2...7.2 m³/h
Resolution	0.1 l/min	0.005 m³/h
Set point SP	0.7...100 l/min	0.04...6 m³/h
Reset point rP	0.2...99.5 l/min	0.01...5.97 m³/h
Analog start point ASP	0...80 l/min	0...4.8 m³/h
Analog end point AEP	20...100 l/min	1.2...6 m³/h
In steps of	0.1 l/min	0.005 m³/h
Volumetric flow quantity monitoring		
Pulse value		0.00001...100 000 m³
Pulse length	[s]	0,0025...2
Temperature monitoring		
Measuring range	[°C]	-20...80
Resolution	[°C]	0.2
Set point SP	[°C]	-19.2...80
Reset point rP	[°C]	-19.6...79.6
Analog start point	[°C]	-20...60
Analog end point	[°C]	0...80
In steps of	[°C]	0.2
Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)		± (0,8 % MW + 0,5 % MEW)
Repeatability		± 0,2% MEW
Temperature monitoring		
Accuracy	[K]	± 2,5 (Q > 5 l/min)

# SM8400

## Magnetic-inductive flow meter

SMK11GGXFRKG/US-100



Reaction times		
Flow monitoring		
Response time	[s]	0.15; (dAP = 0, T19)
Delay time programmable dS, dr	[s]	0...50
Damping process value dAP	[s]	0...5
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 20 (Q > 5 l/min)
Software / programming		
Parameter setting options		Flow monitoring; quantity meter; Preset counter; Temperature monitoring; hysteresis / window; normally open / closed; switching logic; current/voltage/pulse output; Start-up delay; display can be deactivated; Display unit
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9
Profiles		Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis
SIO mode		yes
Required master port class		A
Process data analog		3
Process data binary		2
Min. process cycle time	[ms]	5
Supported DeviceIDs	Type of operation	DeviceID
	default	575
Operating conditions		
Ambient temperature	[°C]	-10...60
Storage temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	DIN EN 60947-5-9	
CPA approval	model number	002MI
	accuracy class	-
	maximum allowable error	± 1,5 % FS
	Q (min)	0,01 m³/h
	Q (t)	-
	Q (max)	6 m³/h
Shock resistance	DIN IEC 68-2-27	20 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	5 g (10...2000 Hz)
MTTF	[years]	145
UL approval	UL approval number	I010
Pressure equipment directive	sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data		
Weight	[g]	673.5
Material	stainless steel (1.4404 / 316L); PBT-GF20; PC; FKM; TPE	

# SM8400



## Magnetic-inductive flow meter

SMK11GGXFRKG/US-100

Materials (wetted parts)	stainless steel (1.4404 / 316L); PEEK; FKM
Process connection	threaded connection Rc 1 Internal thread DN25
<b>Displays / operating elements</b>	
Display	Display unit
	6 x LED, green (l/min, m³/h, l, m³, 10³, °C)
	Switching status
	2 x LED, yellow
	Measured values
	alphanumeric display, 4-digit
	Programming
	alphanumeric display, 4-digit


<b>Remarks</b>	
Remarks	MW = Measured value MEW = Final value of the measuring range
Pack quantity	1 pcs.

## Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



## Connection



OUT1:	Colors to DIN EN 60947-5-2 Switching output Volumetric flow quantity monitoring Pulse output quantity meter signal output Preset counter IO-Link
OUT2:	Switching output Volumetric flow quantity monitoring Switching output Temperature monitoring analog output Volumetric flow quantity monitoring analog output Temperature monitoring Input counter reset Core colors :
BK =	black
BN =	brown
BU =	blue
WH =	white

# SM8400




## Magnetic-inductive flow meter

SMK11GGXFRKG/US-100

### Diagrams and graphs

#### Pressure loss



dP Pressure loss

Q volumetric flow quantity