RU1066


Incremental encoder with solid shaft

RU-2500-I05/S2

Article no longer available - archive entry

Alternative articles: RUP500

When selecting an alternative article and accessories please note that technical data may differ!



1 reference mark
2 M4 Depth 5 mm

Product characteristics		
Resolution		2500 resolution
Shaft design		solid shaft
Shaft diameter	[mm]	6
Application		
Function principle		incremental
Electrical data		
Operating voltage tolerance	[%]	10
Operating voltage	[V]	5 DC
Current consumption	[mA]	150
Outputs		
Electrical design		TTL
Max. current load per output	[mA]	20
Switching frequency	[kHz]	300
Phase difference A und B	[°]	90
Measuring/setting range		
Resolution		2500 resolution
Operating conditions		
Ambient temperature	[°C]	-30...100

RU1066

Incremental encoder with solid shaft

RU-2500-I05/S2

Note on ambient temperature		firmly laid cable: -30 °C
Storage temperature	[°C]	-30...100
Max. relative air humidity	[%]	98
Protection		IP 64

Tests / approvals

Shock resistance		100 g (6 ms)
Vibration resistance		10 g (55...2000 Hz)


Mechanical data

Weight	[g]	545.6
Dimensions	[mm]	Ø 58 / L = 46
Material		aluminum
Max. revolution, mechanical	[U/min]	12000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	6
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20
Fixing flange		Synchro-flange

Electrical connection

Cable: 2 m, PUR; axial

Connector: 1 x Bajonett (ifm 1000.2)



Pin 1	A
Pin 2	A inverted
Pin 3	B
Pin 4	B inverted
Pin 5	L+ sensor
Pin 6	0 index
Pin 7	0 index inverted
Pin 9	L+ (Up)
Pin 10	0V sensor
Pin 11	housing
Pin 12	0V (Un)


RU1066

Incremental encoder with solid shaft

RU-2500-I05/S2

Diagrams and graphs

Pulse diagram



Direction of rotation clockwise (looking at the shaft)