




Control monitor for flow sensors

VS0200/230VAC

Article no longer available - archive entry

Alternative articles: SN0150  
When selecting an alternative article and accessories please note that technical data may differ!



Application		
Application		Flow monitoring; Temperature monitoring
Electrical data		
Operating voltage tolerance	[%]	-10...10
Operating voltage	[V]	< 230 AC
Max. power consumption	[VA]	3
Power-on delay time	[s]	30
Number of channels		1
Outputs		
Electrical design		Relay
Contact rating		4 A, 250 V AC
Switching function flow monitoring		relay energized when flow is present
Switching function temperature monitoring		relay energized when temperature is exceeded
Software / programming		
Adjustment of the switch point		potentiometer
Selection liquids / gases		with slide switch
Switch point setting		potentiometer
Temperature range	[°C]	20...80
Repeatability switch point / measured value	[K]	4

# SN0101



## Control monitor for flow sensors

VS0200/230VAC

### Operating conditions

Ambient temperature	[°C]	0...60
Protection		IP 40
Protection rating terminals		IP 20

### Mechanical data

Housing		housing for DIN rail mounting
Dimensions	[mm]	75 x 55 x 110
Material		plastics

### Displays / operating elements

Display	Function	11 x LED
	Switching status	LED, red


### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection

terminals: 16 x ...2.5 mm<sup>2</sup>

### Connection



- 1: Temperature monitoring  
2: Wire break monitoring  
Core colors :  
BN = brown  
BU = blue  
BK = black  
WH = white  
GY = grey