
# SR0153

### Control monitor for flow sensors



VS3000/24VDC



Application			
Application		Flow monitoring; Temperature monitoring; Wire break monitoring	
Electrical data			
Operating voltage tolerance	[%]	-1010	
Operating voltage	[V]	24 DC	
Current consumption	[mA]	90	
Protection class		III	
Reverse polarity protection		no	
Power-on delay time	[S]	1080; (adjustable (fixed-value resistors terminals 22-23))	
Number of channels		1	
Outputs			
Performance in case of a fault		In case of undervoltage all relays are de-energized, the LED "LOW VOLTAGE/WIRE BREAK-RELAY" lights	
Electrical design		Relay	
Contact rating		4 A (250 V AC / 30 V DC)	
Switching function flow monitoring		relay energized when flow is present and during the power-on delay time	
Switching function temperature monitoring		relay de-energized when temperature is exceeded	
Switching function wire break monitoring		relay de-energized in case of wire-break or short circuit	
Short-circuit proof		no	
Overload protection		no	

## SR0153

## Control monitor for flow sensors



VS3000/24VDC

Reaction times				
Response time	[s]	< 3		
Software / programming				
Adjustment of the switch point		potentiometer		
Selection liquids / gases		wire bridge; on delivery: monitoring of liquids.; for monitoring of gases: link terminals 23 / 24.		
Switch point setting		pote	ntiometer	
Temperature range	[°C]	080		
Repeatability switch point / measured value	[K]	4		
Operating conditions				
Ambient temperature	[°C]	-2	060	
Note on ambient temperature		in case of sufficient free space for convection cooling		
Protection		IP 20		
Tests / approvals				
MTTF	[years]	263		
Mechanical data				
Weight	[g]	233		
Housing		housing for DIN rail mounting		
Dimensions	[mm]	100 x 25 x 103.5		
Material		PBT		
Displays / operating eleme	nts			
Display		Function	11 x LED	
		Switching status	LED, red	
		Switching status	LED, red	
Electrical connection				
Required protection		miniature fuse to IEC60127-2 sheet 1; $\leq$ 5 A; fast acting		
Remarks				
Remarks		Recommendation Check the safe functioning of the unit after a short circuit.		
Pack quantity		1 pcs.		

## SR0153

### Control monitor for flow sensors

VS3000/24VDC

### **Electrical connection**



Combicon connector:

Connection

1 =

2 =

3 =

4 =

5 =

Note

BN =

BU =

BK =

WH =

GY =

