

ST0521




Flow monitor

SCR14AACFPKG/US-100-IPF

Article no longer available - archive entry

Alternative articles: SR5900 + SF2405

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1
------------------------------	------------------------------

Process connection	G 1/4 external thread
--------------------	-----------------------

Application

Media	aggressive media
-------	------------------

Medium temperature [°C]	-25...80
-------------------------	----------

Pressure rating [bar]	5
-----------------------	---

Liquids

Medium temperature [°C]	-25...80
-------------------------	----------

Electrical data

Operating voltage [V]	20...36 DC
-----------------------	------------

Current consumption [mA]	< 45
--------------------------	------

Reverse polarity protection	yes
-----------------------------	-----

Power-on delay time [s]	< 20
-------------------------	------

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1
------------------------------	------------------------------

Outputs

Total number of outputs	1
-------------------------	---

Output signal	switching signal
---------------	------------------

Electrical design	PNP
-------------------	-----

ST0521



Flow monitor

SCR14AACPKG/US-100-IPF

Number of digital outputs		1
Output function		normally open / closed; (configurable)
Max. voltage drop switching output DC [V]		2.5
Permanent current rating of switching output DC [mA]		400
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Measuring/setting range		
Liquids		
Setting range [cm/s]		3...200
Greatest sensitivity [cm/s]		3...40
Accuracy / deviations		
Max. temperature gradient of medium [K/min]		7
Reaction times		
Response time [s]		2...20
Liquids		
Response time [s]		2...20
Software / programming		
Adjustment of the switch point		potentiometer
Operating conditions		
Ambient temperature [°C]		-20...80
Protection		IP 67
Mechanical data		
Material		PBT-GF20
Materials (wetted parts)		PTFE
Process connection		G 1/4 external thread
Displays / operating elements		
Display	Function	11 x LED
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Connector: 1 x M12; coding: A		



ST0521

Flow monitor

SCR14AACFPKG/US-100-IPF



Connection

