

RU-1000-I05/S2E

Article no longer available - archive entry



Resolution	1000 resolution
Shaft design	solid shaft
Shaft diameter [mm]	6

Operating voltage tolerance	[%]	10
Operating voltage	[V]	5 DC
Current consumption	[mA]	150

Electrical design	TTL
Max. current load per output [mA]	20
Switching frequency [kHz]	300
Phase difference A und B [°]	90

Resolution	1000 resolution
------------	-----------------

Ambient temperature	[°C]	-30...100
Note on ambient temperature		firmly laid cable: -30 °C
Storage temperature	[°C]	-30...100
Protection		IP 66

RU1185



Incremental encoder with solid shaft

RU-1000-I05/S2E

Tests / approvals

Shock resistance	100 g (6 ms)
Vibration resistance	10 g (55...2000 Hz)

Mechanical data

Dimensions [mm]	Ø 58 / L = 46
Material	aluminum
Max. revolution, mechanical [U/min]	12000
Max. starting torque [Nm]	1
Reference temperature torque [°C]	20
Shaft design	solid shaft
Shaft diameter [mm]	6
Shaft material	steel (1.4104)
Max. shaft load axial (at the shaft end) [N]	10
Max. shaft load radial (at the shaft end) [N]	20
Fixing flange	Synchro-flange


Electrical connection

Cable: 2 m, PUR; radial

Connector: 1 x (ifm 1000.2)

Diagrams and graphs

Pulse diagram



Direction of rotation clockwise (looking at the shaft)