

ST6600




Flow monitor

SCE18ADBFPKG/PH

Article no longer available - archive entry

Alternative articles: SI5000 + E40104

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Number of inputs and outputs		Number of digital outputs: 1
Process connection		T-piece QL 18 / ST DIN 2353
Application		
Application		high pressure
Media		Liquids
Medium temperature	[°C]	-25...80
Pressure rating	[bar]	300
Electrical data		
Operating voltage	[V]	20...36 DC
Current consumption	[mA]	< 45
Reverse polarity protection		yes
Power-on delay time	[s]	< 20
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 1
Outputs		
Total number of outputs		1
Output signal		switching signal
Electrical design		PNP

ST6600



Flow monitor

SCE18ADBFPKG/PH

Number of digital outputs	1
Output function	normally open / closed; (configurable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	400
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes
Measuring/setting range	
Setting range [cm/s]	3...300
Greatest sensitivity [cm/s]	3...60
Accuracy / deviations	
Max. temperature gradient of medium [K/min]	300
Reaction times	
Response time [s]	1...10
Software / programming	
Adjustment of the switch point	potentiometer
Operating conditions	
Ambient temperature [°C]	-20...80
Protection	IP 67
Mechanical data	
Dimensions [mm]	60 x 41 x 101
Material	PBT-GF20
Materials (wetted parts)	stainless steel (1.4571/316Ti)
Process connection	T-piece QL 18 / ST DIN 2353
Displays / operating elements	
Display	Function11 x LED
Remarks	
Pack quantity	1 pcs.

ST6600




Flow monitor

SCE18ADBFPKG/PH

Electrical connection

Cable: 2 m, PUR; 3 x 0.5 mm², PVC

Connection



BN =	Core colors :
BU =	brown
BK =	blue
	black