


# SU8000

## Ultrasonic flow meter

SUR11HGBFRKG/W/US-100-IPF



installation length with pipe adapter E40152 / E40155: 205 mm  
installation length with pipe adapter E40153 / E40156: 215 mm



### Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1	
Measuring range	0...100 l/min	0...6 m³/h
Process connection	threaded connection G 1 flat seal	

### Application

System	gold-plated contacts	
Application	Totalizer function; for industrial applications	
Installation	connection to pipe by means of an adapter	
Media	water; glycol solutions; Coolants; oils	
Note on media	low-viscosity oils with viscosity: 7...40 mm²/s (40 °C)	high-viscosity oils with viscosity: 30...68 mm²/s (40 °C)
Medium temperature [°C]		-10...80
Pressure rating	16 bar	1.6 MPa

### Electrical data

Operating voltage [V]	19...30 DC; (to SELV/PELV)	
Current consumption [mA]	100	
Min. insulation resistance [MΩ]	100; (500 V DC)	
Protection class	III	
Reverse polarity protection	yes	
Power-on delay time [s]	10	

### Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1	
------------------------------	---	--

# SU8000

## Ultrasonic flow meter

SUR11HGBFRKG/W/US-100-IPF



Inputs		
Inputs		counter reset
Outputs		
Total number of outputs		2
Output signal		switching signal; analog signal; pulse signal; (configurable)
Electrical design		PNP/NPN
Number of digital outputs		2
Output function		normally open / closed; (configurable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250; (per output)
Number of analog outputs		1
Analog current output	[mA]	4...20; (scalable)
Max. load	[Ω]	500
Analog voltage output	[V]	0...10; (scalable)
Min. load resistance	[Ω]	2000
Pulse output		flow rate meter
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Measuring/setting range		
Measuring range	0...100 l/min	0...6 m³/h
Display range	0...120 l/min	0...7.2 m³/h
Resolution	0.1 l/min	0.005 m³/h
Set point SP	0.2...100 l/min	0.01...6 m³/h
Reset point rP	0...99.8 l/min	0...5.99 m³/h
Analog start point ASP	0...80 l/min	0...4.8 m³/h
Analog end point AEP	20...100 l/min	1.2...6 m³/h
Max. flow rate	110 l/min	6.6 m³/h
In steps of	0.1 l/min	0.005 m³/h
Volumetric flow quantity monitoring		
Pulse value		0.1 l...1 000 000 m³
Pulse length	[s]	0,025...2
Temperature monitoring		
Measuring range	[°C]	-10...80
Resolution	[°C]	0.2
Set point SP	[°C]	-9.8...80
Reset point rP	[°C]	-10...79.8
Analog start point	[°C]	-10...62
Analog end point	[°C]	8...80
In steps of	[°C]	0.2

# SU8000

## Ultrasonic flow meter

SUR11HGBFRKG/W/US-100-IPF



### Accuracy / deviations

#### Flow monitoring

Accuracy (in the measuring range)	water: < ± (3 % MW + 0,2 % MEW); glycol (35 %), oil (viscosity 68 mm²/s at 40 °C): < ± (5 % MW + 0,5 % MEW)
Repeatability	0,2 l/min; 12 l/h; 0,012 m³ /h

#### Temperature monitoring

Accuracy	[K]	± 3 (Q > 1 l/min)
----------	-----	-------------------

### Reaction times

#### Flow monitoring

Response time	[s]	0.25; (dAP = 0)
Delay time programmable dS, dr	[s]	0...50
Damping process value dAP	[s]	0...1

#### Temperature monitoring

Dynamic response T05 / T09	[s]	T09 = 70 (Q > 5 l/min); (water)
----------------------------	-----	---------------------------------

### Software / programming

Parameter setting options	Flow monitoring; quantity meter; Preset counter; Temperature monitoring
---------------------------	---

### Operating conditions

Ambient temperature	[°C]	-10...60
Storage temperature	[°C]	-25...80
Protection		IP 67

### Tests / approvals

EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5 kV
	EN 61000-4-6 HF conducted	10 V
CPA approval	model number	001US
	accuracy class	3
	maximum allowable error	-
	Q (min)	0,3 m³/h
	Q (t)	0,54 m³/h
	Q (max)	6 m³/h
Shock resistance	DIN IEC 68-2-27	20 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	5 g (10...2000 Hz)
MTTF [years]		185
Pressure equipment directive		sound engineering practice; can be used for group 2 fluids; group 1 fluids on request

### Mechanical data


Weight	[g]	1713.5
Material		housing: AlMgSi0.5 anodized; sealing: FKM; PA 6.6; cover film: PA
Materials (wetted parts)		stainless steel (1.4404 / 316L); FKM; PES; Centellen 200
Process connection		threaded connection G 1 flat seal

# SU8000



## Ultrasonic flow meter


SUR11HGBFRKG/W/US-100-IPF

Displays / operating elements	
Display	Display unit Switching status Measured values Programming
	6 x LED, green (l/min, m <sup>3</sup> /h, l, m <sup>3</sup> , 10 <sup>3</sup> , °C) 2 x LED, yellow alphanumeric display, 4-digit alphanumeric display, 4-digit
Accessories	
Items supplied	sealings: 2, Centellen
Accessories (optional)	adapter for pipe: 1 x R 1/2, stainless steel, E40179 adapter for pipe: 1 x R 3/4, stainless steel, E40180 adapter for pipe: 1 x R 1/2, brass, E40152 adapter for pipe: 1 x R 3/4, brass, E40153
Remarks	
Remarks	MW = Measured value MEW = Final value of the measuring range sealing: only with supplied Centellen seals
Pack quantity	1 pcs.
Electrical connection	
Connector: 1 x M12; coding: A; Moulded body: brass, Optalloy-plated; Contacts: gold-plated	
	
Connection	
	
OUT1:	Switching output Volumetric flow quantity monitoring Pulse output quantity meter signal output Preset counter
OUT2/InD:	Switching output Volumetric flow quantity monitoring / Temperature monitoring analog output Volumetric flow quantity monitoring / Temperature monitoring Input counter reset



### Diagrams and graphs

#### Pressure loss



dP Pressure loss

Q volumetric flow quantity