


# SUH200



## Ultrasonic flow meter

SUC251JBFRKG/US



Product characteristics	
Measuring range	1...240 l/min    60...14400 l/h    0.051...12.202 m/s    0.06...14.4 m³/h
Nominal diameter	DN25 (1")
Process connection	Clamp 1" DIN 32676 series C (ASME BPE)
Application	
Special feature	gold-plated contacts
Media	ultra-pure water; water; water-based media; edible oils
Note on media	water-based media: for media with >10 % additives, the repeatability is the only available value edible oils: palm oil, soy oil, rapeseed oil, sunflower oil, peanut oil, olive oil and others
Medium temperature [°C]	-20...100
Min. burst pressure	75 bar    7.5 MPa
Pressure rating	25 bar    2.5 MPa
Note on pressure rating	take into account the pressure resistance of the bracket and the seal used for clamp connection
Vacuum resistance [mbar]	-1000
Electrical data	
Operating voltage [V]	18...32 DC; (to SELV/PELV)
Current consumption [mA]	< 75
Protection class	III
Reverse polarity protection	yes

# SUH200



## Ultrasonic flow meter

SUC251JBFRKG/US

Power-on delay time	[s]	5			
Measuring principle		ultrasonic			
<b>Inputs / outputs</b>					
Total number of inputs and outputs		2			
<b>Inputs</b>					
Inputs		OUT2	counter reset		
<b>Outputs</b>					
Total number of outputs		2			
Output signal		OUT1	switching signal; pulse signal; diagnostic signal; totalizer switching signal; frequency signal; IO-Link		
		OUT2	switching signal; pulse signal; diagnostic signal; totalizer switching signal; analog signal		
Electrical design		PNP/NPN			
Min. load resistance	[Ω]	2000			
Pulse output		flow rate meter			
Short-circuit protection		yes			
Type of short-circuit protection		yes (non-latching)			
Overload protection		yes			
<b>Analog</b>					
Number of analog outputs		1			
Analog current output	[mA]	4...20			
Max. load	[Ω]	500			
<b>Digital</b>					
Number of digital outputs		2			
Output function		normally open / closed; (configurable)			
Max. voltage drop switching output DC	[V]	2			
Permanent current rating of switching output DC	[mA]	100			
Switching frequency DC	[Hz]	0...10000			
<b>Measuring/setting range</b>					
Measuring range		1...240 l/min	60...14400 l/h	0.051...12.202 m/s	0.06...14.4 m³/h
Display range		-288...288 l/min	-17280...17280 l/h	-14.642...14.642 m/s	-17.28...17.28 m³/h
Resolution		0.1 l/min	1 l/h	0.001 m/s	0.002 m³/h
Set point SP		2.3...240 l/min	139...14400 l/h	0.118...12.202 m/s	0.139...14.4 m³/h
Reset point rP		1.1...238.8 l/min	64...14325 l/h	0.055...12.139 m/s	0.064...14.325 m³/h
Analog start point ASP		-240...192 l/min	-14400...11522 l/h	-12.202...9.763 m/s	-14.4...11.522 m³/h
Analog end point AEP		-192...240 l/min	-11522...14400 l/h	-9.763...12.202 m/s	-11.522...14.4 m³/h
Low flow cut-off LFC		1...12 l/min	60...720 l/h	0.051...0.61 m/s	0.06...0.72 m³/h
Frequency end point, FEP		48.1...240 l/min	2889...14400 l/h	2.448...12.202 m/s	2.89...14.4 m³/h
Frequency at the end point FRP	[Hz]	1...10000			

# SUH200



## Ultrasonic flow meter

SUC251JBFRKG/US

<b>Volumetric flow quantity monitoring</b>		
Pulse length	[s]	0.002...2
Pulse value		0.02...99990000 l
<b>Temperature monitoring</b>		
Measuring range	[°C]	-20...100
Display range	[°C]	-44...124
Resolution	[°C]	0.1
Set point SP	[°C]	-19.6...100
Reset point rP	[°C]	-20...99.6
Analog start point	[°C]	-20...76
Analog end point	[°C]	4...100
Frequency start point, FSP	[°C]	-20...76
Frequency end point, FEP	[°C]	4...100
Frequency at the end point FRP	[Hz]	1...10000
<b>Accuracy / deviations</b>		
<b>Flow monitoring</b>		
Accuracy (in the measuring range)	edible oils	± (5,0 % MW + 1,0 % MEW)
	water	± (1,0 % MW + 0,5 % MEW)
Repeatability		± 0,2 % MEW
<b>Temperature monitoring</b>		
Accuracy	[K]	± 2,5 (Q > 5 % MEW)
Temperature coefficient [% of the span / 10 K]		0,2
<b>Reaction times</b>		
<b>Flow monitoring</b>		
Response time	[s]	< 0.25; (dAP = 0, T09)
Damping process value dAP	[s]	0...5
<b>Temperature monitoring</b>		
Dynamic response T05 / T09	[s]	5,7 / 86
<b>Software / programming</b>		
Diagnostic functions		direction of flow detection; signal quality
<b>Interfaces</b>		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1.3
SDCI standard		IEC 61131-9: 2013-07
Profiles	BLOB	Binary Large Object transfer
	Common - I&D	Identification and Diagnosis
Required master port class		A
Process data analog		3
Process data binary		2
Min. process cycle time	[ms]	9.6

# SUH200



## Ultrasonic flow meter

SUC251JBFRKG/US

IO-Link process data (cyclical)	Function	bit length
	totalizer	32
	Flow monitoring	32
	Temperature monitoring	32
	status	4
	Output 1	1
	Output 2	1
Supported DeviceIDs	Type of operation	DeviceID
	default	1750

Operating conditions		
Ambient temperature	[°C]	-20...60
Storage temperature	[°C]	-25...80
Protection		IP 69K

Tests / approvals		
EMC	DIN 61326-1:2021	
CPA approval	model number	003US
	accuracy class	1,5
Shock resistance	DIN IEC 68-2-27	20 g (11ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000Hz)
MTTF	[years]	160
UL approval	UL approval number	I034
	File number UL	E174189
Pressure equipment directive	can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight	[g]	637.1
Housing		rectangular
Inlet pipe length		5 x DN
Outlet pipe length		1 x DN
Dimensions	[mm]	175 x 50.4 x 73.8
Material		housing: stainless steel (1.4404 / 316L); Display: PFA; sealing Display: FKM; connector: PBT
Materials (wetted parts)		Pipe section: stainless steel (1.4404 / 316L)
Nominal diameter		DN25 (1")
Process connection		Clamp 1" DIN 32676 series C (ASME BPE)
Process connection suitable for pipe standard		1" / Ø 25,4 mm x 1,65 mm (DIN 11866 series C); (DIN EN 10357 Series D)
Surface characteristics Ra/Rz of the wetted parts		Ra < 0.8 µm

Displays / operating elements		
Display		Color display 1,44", 128 x 128 pixels
	Switching function	2 x LED, yellow
	diagnosis	1 x LED, three-color

Remarks		
Remarks	MW = Measured value	
	MEW = Final value of the measuring range	
	pulse and totalizer signal are only available for one of the two outputs	
	the accuracy indications are adhered to over the entire application area	

# SUH200



## Ultrasonic flow meter

SUC251JBFRKG/US

Pack quantity


1 pcs.

### Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



### Connection




1 (L+)	L+	
2 (OUT2)	MP2	DO2, AO, DI
3 (L-)	L-	
4 (OUT1)	MP1	DO1, FO, IO-Link

AO: analog output; DI: digital input; DO: digital output; FO: Frequency output; MP: multi-function connection

### Diagrams and graphs

Note on pressure loss




# SUH200

## Ultrasonic flow meter

SUC251JBFKRG/US



derating ambient temperature



- 1 Ambient temperature
- 2 Medium temperature