


Temperature transmitter

TCC150K1ER12-A-DKG/US



- 1 LED
- 2 Gasket FKM (for sealing on the back - not pressure resistant) / removable
- 3 pre-mounted PEEK sealing ring (removable) / metallic sealing area

A³ CE CRN cUL_{us} LISTED EC 1935/2004 EHEDG Certified FDA IO-Link UK CA

Product characteristics

Number of inputs and outputs	Number of digital outputs: 1; Number of analog outputs: 1
Measuring range	-25...160 °C -13...320 °F
Communication interface	IO-Link
Process connection	threaded connection G 1/2 sealing cone
Installation length EL [mm]	150

Application

System	gold-plated contacts
Measuring element	1 x Pt 1000
Reference element	1 x NTC
Media	liquids and gases
Pressure rating [bar]	160

Electrical data

Operating voltage [V]	18...32 DC; (cULus - Class 2 source required)
Current consumption [mA]	10; (24 V)
Protection class	III

TCC541



Temperature transmitter

TCC150K1ER12-A-DKG/US

Reverse polarity protection		yes
Power-on delay time	[s]	6
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs	Number of digital outputs: 1; Number of analog outputs: 1	
Outputs		
Total number of outputs		2
Output signal	analog signal; IO-Link; calibration check status	
Electrical design	PNP/NPN	
Number of digital outputs		1
Output function	normally closed; (diagnostic signal)	
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	100
Diagnostic output	calibration check status and error diagnostics	
Number of analog outputs		1
Analog current output	[mA]	4...20
Max. load	[Ω]	(Ub - 15 V) × 50
Short-circuit protection		yes
Type of short-circuit protection	yes (non-latching)	
Overload protection		yes
Measuring/setting range		
Measuring range	-25...160 °C	-13...320 °F
Note on measuring range	scalable	
Factory setting	-10...150 °C / 14...302 °F	
Calibration check limit	[K]	0.5...3
In steps of	[K]	0.05
Resolution		
Resolution of analog output	[K]	0.05
Accuracy / deviations		
Precision analog output	[K]	± 0,2
Precision IO-Link	[K]	± 0,2
Temperature coefficient analog output	< ± 0,02; (In case of deviation from the reference condition 25 ± 5 °C) [% of the span / 10 K]	
Temperature coefficient IO-Link	< ± 0,01; (In case of deviation from the reference condition 25 ± 5 °C) [% of the span / 10 K]	
Reaction times		
Dynamic response T05 / T09	[s]	1,5 / 4
Software / programming		
Parameter setting options	Display unit; scaling of the analog output; calibration check limit; switching logic diagnostic output; simulation mode	

TCC541



Temperature transmitter

TCC150K1ER12-A-DKG/US

Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9 CDV
Profiles		Digital Measuring Sensor, Common Profile, Blob Transfer
SIO mode		yes
Required master port class		A
Process data analog		1
Process data binary		1
Min. process cycle time	[ms]	4.4
IO-Link resolution temperature	[K]	0.01
Supported DeviceIDs	Type of operation	DeviceID
	default	1129
Operating conditions		
Ambient temperature	[°C]	-25...70
Note on ambient temperature		max. internal device temperature: 125 °C
Storage temperature	[°C]	-40...100
Protection		IP 68; IP 69K
Tests / approvals		
EMC		DIN EN 61000-6-2 DIN EN 61000-6-3
Shock resistance		DIN EN 68000-2-27
Vibration resistance		DIN EN 60068-2-6
MTTF	[years]	329
Note on approval		Factory certificate available as download at www.factory-certificate.ifm
UL approval	UL approval number	K021
	File number UL	E217884
Mechanical data		
Weight	[g]	463
Dimensions	[mm]	Ø 50 / L = 244
Material		stainless steel (1.4404 / 316L); PEI; FKM; PFA
Materials (wetted parts)		stainless steel (1.4404 / 316L); PEEK
Tightening torque	[Nm]	30...50
Process connection		threaded connection G 1/2 sealing cone
Surface characteristics Ra/Rz of the wetted parts		Ra: < 0.8
Probe diameter	[mm]	6
Installation length EL	[mm]	150
Remarks		
Remarks		MS = set measuring span cULus - Class 2 source required
Pack quantity		1 pcs.

TCC541



Temperature transmitter


TCC150K1ER12-A-DKG/US

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT2: analog output

OUT1: Diagnostic output / IO-Link