

TA3437




Temperature transmitter

TA-123.LDR12-A-ZVG/US/

Article no longer available - archive entry

Alternative articles: TA2517 or TA2537

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Number of inputs and outputs	Number of analog outputs: 1	
Measuring range	0...100 °C	32...212 °F
Process connection	threaded connection G 1/2 external thread	
Installation length EL [mm]	87.5	

Application

System	gold-plated contacts	
Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)	
Media	liquids and gases	
Medium temperature	< 150; (< 40 min) °C	< 302; (< 40 min) °F
Pressure rating [bar]	300	
Note on pressure rating	sensor	
Minimum installation depth [mm]	When mounted in adapters the specifications of the adapter data sheet apply.	
	15	

Electrical data

Operating voltage [V]	10...30 DC; (to SELV/PELV)
Protection class	III
Reverse polarity protection	yes

Inputs / outputs

Number of inputs and outputs	Number of analog outputs: 1
------------------------------	-----------------------------

Outputs

Total number of outputs	1
Output signal	analog signal
Number of analog outputs	1
Analog current output [mA]	4...20
Max. load [Ω]	500

TA3437



Temperature transmitter

TA-123.LDR12-A-ZVG/US/

Overload protection	yes	
Measuring/setting range		
Probe length L [mm]	47.5	
Measuring range	0...100 °C	32...212 °F
Resolution		
Resolution of analog output [K]	0.02	
Accuracy / deviations		
Precision analog output [K]	± 0,1 (60°C / 140°F) / ± 0,3 (0...100°C / 32...212°F)	
Temperature coefficient [% of the span / 10 K]	< ± 0,1; (In case of deviation from the reference condition 25 ± 5 °C)	
Reaction times		
Dynamic response T05 / T09 [s]	1 / 3; (according to DIN EN 60751)	
Operating conditions		
Ambient temperature [°C]	-25...70	
Storage temperature [°C]	-40...100	
Protection	IP 68; IP 69K	
Tests / approvals		
EMC	DIN EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	DIN EN 61000-4-4 Burst	2 kV
	DIN EN 61000-4-5 Surge	0,5/1 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	10 g (10...2000 Hz)
Mechanical data		
Weight [g]	228	
Dimensions [mm]	Ø 30 / L = 180.5	
Material	stainless steel (1.4404 / 316L); stainless steel (1.4301 / 304); stainless steel (1.4305 / 303); PA	
Materials (wetted parts)	stainless steel (1.4404 / 316L)	
Tightening torque [Nm]	30...50	
Process connection	threaded connection G 1/2 external thread	
Installation length EL [mm]	87.5	
Remarks		
Remarks	referring to UL: for use on a low voltage circuit with overcurrent protection	
	in accordance with UL873 tab. 28.1 or I _{max} = 100/U _b (U _b = voltage of the circuit)	
	The values for accuracy apply to flowing water.	
Pack quantity	1 pcs.	

TA3437



Temperature transmitter

TA-123.LDR12-A-ZVG/US/

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

