




## Temperature sensor with process connection

TM-050KCED10- /US/ /V

Article no longer available - archive entry

Alternative articles: TM4511 + E33403

When selecting an alternative article and accessories please note that technical data may differ!



- 1 Aseptoflex thread
- 2 Aseptoflex sealing edge



EHEDG Certified

### Product characteristics

Measuring range	-40...150 °C	-40...302 °F
Process connection	G 1 Aseptoflex Vario	
Installation length EL [mm]	63.8	

### Application

System	gold-plated contacts	
Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)	
Application	hygienic systems	
Media	liquids and gases	
Pressure rating [bar]	50	
Minimum installation depth [mm]	15	

### Electrical data

Protection class	III
------------------	-----

### Measuring/setting range

Probe length L	[mm]	50	
Measuring range		-40...150 °C	-40...302 °F

### Accuracy / deviations

Accuracy [K]	± (0,15 K + 0,002 x t )
--------------	-------------------------

### Reaction times

Dynamic response T05 / T09 [s]	5 / 14; (according to DIN EN 60751)
--------------------------------	-------------------------------------

### Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 68; IP 69K

### Mechanical data

Weight [g]	229
Material	stainless steel (1.4404 / 316L)

TM0061



Temperature sensor with process connection


TM-050KCED10- /US/ /V

Materials (wetted parts)	stainless steel (1.4404 / 316L)
Process connection	G 1 Aseptoflex Vario
Surface characteristics Ra/Rz of the wetted parts	Ra: < 0.6
Probe diameter [mm]	10
Installation length EL [mm]	63.8

Remarks	
Remarks	The values for accuracy apply to flowing water. The 3-A qualification is only valid if adapters with 3-A qualification are used for installation. cULus - Class 2 source required
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

