


TM4101



Temperature sensor with process connection

TM-025KFBR14-

/US/



Product characteristics

Measuring range	-40...150 °C	-40...302 °F
Process connection	threaded connection G 1/4 external thread	
Installation length EL [mm]	25	

Application

Special feature	gold-plated contacts	
Measuring element	1 x Pt 100; (to DIN EN 60751, class A)	
Media	liquids and gases	
Pressure rating	400 bar	40 MPa

Electrical data

Protection class	III	
------------------	-----	--

Measuring/setting range

Probe length L [mm]	12	
Measuring range	-40...150 °C	-40...302 °F

Accuracy / deviations

Accuracy [K]	$\pm (0,15 K + 0,002 x t)$	
--------------	-----------------------------	--

Reaction times

Dynamic response T05 / T09 [s]	1 / 3; (according to DIN EN 60751)	
--------------------------------	------------------------------------	--

Operating conditions

Ambient temperature [°C]	-25...80	
Storage temperature [°C]	-40...100	
Protection	IP 68; IP 69K	

Tests / approvals

Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF [years]	22831.05	

Mechanical data

Weight [g]	61	
Housing	tubular	
Dimensions [mm]	Ø 24.5 / L = 48	
Material	stainless steel (1.4404 / 316L)	

TM4101



Temperature sensor with process connection

TM-025KFBR14- /US/

Materials (wetted parts)		stainless steel (1.4404 / 316L); FKM
Tightening torque	[Nm]	35
Process connection		threaded connection G 1/4 external thread
Probe diameter	[mm]	6
Installation length EL	[mm]	25

Remarks

Remarks	cULus - Class 2 source required	
	The values for accuracy apply to flowing water.	
Pack quantity		1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection

